

Previously known as: Powerflex® 80-100



Multi Purpose



Heavy Duty

## Superb mechanical performance with comfort and a sure grip

- The Ansell ActivArm<sup>®</sup> 80-100 glove is designed for use in a wide range of handling and carrying applications
- For optimum productivity and safety in construction, transport, and shipping and receiving, the ActivArm<sup>®</sup> 80-100 glove is the smart and logical choice
- Thanks to its natural rubber coating, the Ansell ActivArm<sup>®</sup> 80-100 glove delivers excellent overall mechanical performance for maximal protection and durability
- The latex coating's raised crinkle finish gives the glove an excellent grip in both dry and wet conditions
- The automatic knitted liner delivers an optimally tensioned inner surface for superb fit and flexibility
- Available in sizes 6 through 10 in North America

### Industries

- Machinery and Equipment

### Applications

- Seizing rough blocs and cylinders
- Seizing and finishing structural parts
- Loading and unloading rough parts or boxes
- Picking parts and accessories
- Final assembly
- Loading raw material
- Unloading worked parts



Previously known as: Powerflex® 80-100

### Key Features

- Crinkled finished coating for an excellent dry or wet grip for better safety and productivity

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
ActivArm® 80-100	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Natural Latex Rubber <b>Liner Material:</b> Cotton, Polyester <b>Cuff Style:</b> Knitwrist	10	6, 7, 8, 9, 10	235 - 280 mm/ 9.25-11.02 inches	Blue	<ul style="list-style-type: none"> <li>• 12 pairs in a bag, 12 bags in a carton</li> </ul>

### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
 Riverside Business Park  
 Blvd International, 55  
 1070 Brussels, Belgium  
 T: +32 (0) 2 528 74 00  
 F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
 111 Wood Avenue South,  
 Suite 210  
 Iselin, NJ 08830, USA  
 T: +1 800 800 0444  
 F: +1 800 800 0445

#### Australia

Ansell Limited  
 Level 3,678 Victoria Street,  
 Richmond, Vic, 3121  
 Australia  
 T: +61 1800 337 041  
 F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
 (Malaysia) Sdn Bhd  
 Prima 6, Prima Avenue  
 Block 3512, Jaijan Teknokrat 6  
 T: +603 8310 6688  
 F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
 Blvd. Bernardo Quintana No. 7001-C,  
 Q7001 Torre II,  
 Suites 1304, 1305 y 1306,  
 Col. Centro Sur, c.p. 76079  
 Queretaro, Qro. Mexico  
 T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
 105 Lauder  
 Cowansville, QC J2K 2K8  
 Canada  
 T: +1 800 363 8340  
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.