




TWO GANG - RAYNTITE® FLIP COVERS

**Two Gang RAYNTITE® Metal Flip Covers
(1) Duplex & (1) GFCI**

D16



Catalog #: 5033-0

APPLICATIONS

For use whenever weatherproof protection is required for an outdoor receptacle.
N/A

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Self closing lids assure weatherproof protection when the receptacle is not in use
- Padlockable, 1/4 in. diameter hole
- May be mounted to box or device
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package

UL LISTED

File E195978

CSA

C22.2 No. 18

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Gangs: 2

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.658

PACKAGING

Package Type: Shrink
 Std. Pkg.: 6
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 65.80
 Ship Carton Length (in.): 10.56
 Ship Carton Width (in.): 6.50
 Ship Carton Height (in.): 8.50
 Ctn Weight (Lbs.): 3.95
 Pallet Qty: 840.00
 UPC Number: 050169503300
 I2of5: 50050169503305