



Part Detail

Agency Compliance	UL Listed, CSA Certified
Motor Type	Permanent Split Capacitor
Motor Enclosure	Open Air-Over
NEMA Frame Size	48Y
Motor Insulation	B
Horsepower (Typ.)	1/6 hp
Voltage	115
Full Load Amps	2.2
RPM	1,140 rpm
Nominal Efficiency	49.6 %
Hertz (Cycle)	60 Hz
Motor Phase	1