



4YU27 - Motor Spec Sheet



Part Detail

Agency Compliance	UL/cUL Recognized
Motor Type	Permanent Split Capacitor
Motor Enclosure	Open Air-Over
NEMA Frame Size	48Y
Motor Insulation	B
Horsepower (Typ.)	1/4 hp
Voltage	115
Full Load Amps	3.6
RPM	1,725 rpm
Nominal Efficiency	58.3 %
Hertz (Cycle)	60 Hz
Motor Phase	1