

**Part Detail**

<b>Agency Compliance</b>	UL Listed, CSA Certified
<b>Motor Type</b>	Permanent Split Capacitor
<b>Motor Enclosure</b>	Open Air-Over
<b>NEMA Frame Size</b>	Nonstandard
<b>Motor Insulation</b>	B
<b>Horsepower (Typ.)</b>	1/8 hp
<b>Voltage</b>	115
<b>Full Load Amps</b>	2.6/2.3/1.4
<b>RPM</b>	1,550 rpm, 1,300 rpm, 1,050 rpm
<b>Nominal Efficiency</b>	24 %
<b>Hertz (Cycle)</b>	60 Hz
<b>Motor Phase</b>	1