


**STRAIGHT STRAIN RELIEF CONDUIT AND CORD CONNECTORS****Straight Strain Relief Cord Connectors Steel/Malleable Iron**
N/A**B57**

Catalog #: 3703-1

APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

All steel/malleable construction provides mechanical strength
Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
Washers have cable size range imprinted for identification - eliminates misidentifying inventory
Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
All metallic components are zinc electro plated for added corrosion protection
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation
3/8 in. to 1 in. Steel bodies; 1-1/4 in. to 1-1/2 in. Malleable Iron bodies
3/8 in. to 1 in. Steel nuts; 1-1/4 in. to 1-1/2 in. Malleable Iron nuts
N/A

CULUS

UL File E195973

GENERAL PRODUCT INFORMATION

Trade Size: 3/4 in.
Cable Range: .250 - .375
Form Size: 3

DRAWING DIMENSIONS

Dimension A: 1-13/32 in.
Dimension B: 9/16 in.
Thread Spec. B: 3/4 in. - 14 NPT
Dimension C: 1-31/64 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 25
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 20.60
Ship Carton Length (in.): 8.25
Ship Carton Width (in.): 5.00
Ship Carton Height (in.): 4.00
Ctn Weight (Lbs.): 5.15
UPC Number: 050169370315
I2of5: 50050169370310