

CHROME SLT®

Velcro® cuff for a comfortable and precise fit

Goatskin leather palm provides a traditional style of comfort

Reinforced thumb saddle

HPPE blend palm provides industry-leading cut resistance (interior layer)

OilGuard® treated leather helps delay saturation issues

Pre-curved construction for better fit

Back-of-hand impact guards provide ANSI/ISEA 138 Level 1 protection on knuckles and fingers

Form-fitting, quality materials

High dexterity

360° C100 Thinsulate™ interior liner keeps hands warm



4064 Chrome SLT® Winter

PROTECTION ZONES:

		ANSI/ISEA CUT	GRAM SCORE
		A4	2036
		ANSI/ISEA PUNCTURE	ANSI/ISEA 138
		5	1
		CE	
		2X44EP	

ATTRIBUTES:

Style:	Mechanics
Grip:	Dry or light oil
Cuff Style:	Velcro®
Sizes:	7/S through 12/3XL

FEATURES:

HexArmor® Chrome SLT® gloves are built for a wide array of applications. Each product in the series was crafted to fit the hand with a specific purpose. With multiple styles and various safety features, you can be confident that the Chrome SLT® will keep your hands protected against almost any hazard. Our Chrome SLT® gloves were designed with ultimate comfort in mind, providing unsurpassed dexterity while maintaining cut and puncture resistance. With options for cold weather protection, your hands can stay safe and comfortable in any environment.

HexArmor®

Call **1-877-MY ARMOR** or visit **hexarmor.com**

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.

Protected by patents and patents pending