

## These black chemical resistant gloves offer one glove with the benefits of two. Multi-barrier chemical protection

- These acid-resistant gloves offer a nitrile and neoprene barrier that provides advanced chemical protection from acids to hydrocarbons and beyond
- These AlphaTec® 53-001 black chemical resistant gloves have 'Type A' chemical protection under EN ISO 374:2016/li>
- MICROCHEM™ Chemical Barrier Technology combines polymers in proprietary blends or multi-layer structures specific to their application, providing superior protection to wearers
- ANSELL GRIP™ Technology for the handling of wet or oily parts providing enhanced dexterity, grip and comfort

### Industries

- Automotive
- Metal fabrication
- Chemical
- Oil and gas
- Aerospace

### Applications

- Chemical processing and preparation
- Cleaning
- Delivery of parts to production line



### Key Features

- Innovative multi-layer polymer design - nitrile/neoprene/nitrile layers
- Provides chemical protection against a wide range of chemicals from acids and bases to hydrocarbons and organic solvent
- Tested according to EN ISO 374:2016, permeation time >30 minutes against 13 chemicals out of 18 listed
- Features the latest MICROCHEM™ chemical barrier technology providing superior protection for use in hazardous environments
- ANSELL GRIP™ Technology for the handling of wet or oily parts providing enhanced dexterity, grip and comfort
- Inner soft nylon liner for comfort and increased mechanical protection
- Oeko-Tex® Standard 100 Approved
- For complete chemical permeation information, please visit: [www.ansellguardianpartner.com](http://www.ansellguardianpartner.com)

### Technologies



**ANSELL GRIP™**  
Ansell Grip Technology



**MICROCHEM™**  
Chemical Barrier Technology



### Performance Standards



### Specifications

BRAND   STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 53-001	Nylon, Neoprene and Nitrile, Ansell Grip™	6, 7, 8, 9, 10, 11	350 mm / 13 inches	Black	• 6 pairs in a bag; 12 bags in a carton

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.