

# Pin & Sleeve Devices

## Accessories



- Back box features heavy duty cast aluminum construction with a durable enamel finish
- Adapter plates allow receptacles and inlets to be mounted to back boxes
- Cast aluminum direct mount back boxes permit receptacles to be mounted directly to box without adapter plate
- Closure caps provide a watertight seal for male plugs and flanged inlets when not mated

## NEMA Type 1 Portable Outlet Box Cover Plates



For Use With	Hub Size In.	Back Boxes			Adapter Plates	Direct Mount Back Boxes
		For Mounting Receptacles and Inlets				
		15° Angle	Feed-Thru	Four-Way		
20/30A	3/4"	<b>BB201WA*</b>	<b>FT202WA*</b>	—	<b>AP2030</b>	<b>DM20301</b>
	1"	<b>BB301WA*</b>	<b>FT302WA**</b>	—		—
60A	1 1/4"	<b>BB601WA*</b>	—	—	<b>AP60</b>	<b>DM602</b>
	1 1/2"	<b>BB602WA*</b>	—	<b>FW60100A**</b>		—
100A	1 1/2"	<b>BB1001WA*</b>	—	<b>FW60100A**</b>	<b>AP100</b>	—
	2"	<b>BB1002WA*</b>	—	—		—

Note: \*Adapter plates: 20/30A devices require AP2030, 60A devices require AP60 and 100A devices require AP100 adapter plates, ordered separately.

\*\*Requires AP60 adapter plate to mount 60A receptacle or inlet. 100A receptacle mounts directly to box. 100A inlet does not mount to this box.

Closure Caps	
For Use With	Catalog Number
16/20A	3-Wire 4-Wire 5-Wire
	<b>CC320A</b> <b>CC420A</b> <b>CC520</b>
30/32A	3 & 4-Wire 5-Wire
	<b>CC330</b> <b>CC530</b>
60/63A	3, 4 & 5-Wire 5-Wire
	<b>CC560</b>
100/125A	3, 4 & 5-Wire 5-Wire
	<b>CC510</b>

## Product Dimensions Inches (mm)

Back Boxes					Adapter Plates			Direct Mount Back Boxes	
20/30A		60A	60/100A	100A	20/30A	60A	100A	20/30A	60A
15° Angle	Feed-Thru	15° Angle	15° Angle	15° Angle	20/30A	60A	100A	20/30A	60A
A 5.12" (130.2)	8.25" (209.6)	7.25" (184.2)	8.75" (222.3)	8.12" (206.4)	3.76" (96.4)	4.51" (115.6)	5.52" (141.5)	5.07" (130.0)	5.81" (149.0)
B 4.00" (101.6)	3.06" (77.8)	5.25" (133.4)	9.75" (247.7)	6.75" (171.5)	3.13" (80.3)	3.88" (99.5)	4.87" (124.9)	3.38" (82.0)	4.28" (110.0)
C 4.19" (106.4)	7.14" (181.4)	6.00" (152.4)	7.75" (196.9)	6.88" (174.6)	2.76" (70.8)	3.03" (77.7)	4.25" (109.0)	4.13" (106.0)	4.56" (117.0)
D 3.75" (95.3)	4.50" (114.3)	4.50" (114.3)	6.75" (171.5)	5.50" (139.7)	2.36" (60.5)	3.35" (85.9)	3.94" (101.0)	3.62" (92.0)	4.58" (117.0)
E 3.00" (76.2)	3.75" (95.3)	3.75" (95.3)	6.00" (152.4)	4.75" (120.7)	0.22" (5.6) Dia.	0.22" (5.6) Dia.	0.22" (5.6) Dia.	—	—
F 4.00" (101.6)	3.13" (79.5)	6.19" (157.2)	—	6.94" (176.2)	0.18" (4.6) Dia.	0.18" (4.6) Dia.	0.18" (4.6) Dia.	—	—
G* 30.0" (492)	48.0" (787)	80.0" (1312)	210.0" (3444)	130.0" (2132)	—	—	—	20.0" (328.0)	40.0" (656.0)

Note: \*Capacity cu. in. (cm3).

