



R-161

High visibility impact protection with comfortable padded palm.



Impact

Abrasion Protection

Chemical Protection



Cut

Ergonomic Protection



Vibration



Light Duty

Impact protection with synthetic red leather padded palm and touchscreen compatibility for comfort and ease-of-use.

The Ringers 161 Medium Duty Impact glove combines protection against impact hazards with enhanced durability and comfort due to a synthetic leather padded palm.

- Developed with Ringers' F3 Technology™ and patented TPR design for superior dexterity and comfort.
- Touchscreen compatible index, middle and thumb tips lessen the need to remove gloves.
- High visibility and hook and loop pull tab closure provides added security on the job.



Industries

- Manufacturing
- Mining
- Automotive
- Automotive Aftermarket
- Oil and gas
- Recycling and Waste Disposal
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

Applications

- General Purpose Auto Aftermarket
- Handling structural and body components
- Body painting including surface inspection
- Applying sealers, touching up
- Body panel repair and replacement
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Seizing structural and body parts
- Equipment maintenance and repair
- Assembly and disassembly of equipment
- Final assembly
- Final inspection
- Signalling/Positioning
- Operating of heavy machinery

WWW.ANSELL.COM

Ansell



R-161

High visibility impact protection with comfortable padded palm.

Key Features

- TPR impact protection on top of hand and fingers
- Flexible knuckle TPR design with two detached fingers
- Durable synthetic leather palm for enhanced grip
- Padded palm for comfort
- Secure cuff closure with hook and loop rubber pull tab
- Reinforced thumb, index, and middle finger tips
- Wrap around index finger protecting wear and tear zone
- Touchscreen compatible index, middle and thumb tips
- High visibility for increased safety

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COLOR	PACKAGE
RINGERS R161	Liner Material: N/A Cuff Style: Adjustable		7, 8, 9, 10, 11, 12, 13	Hi Viz	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.



