



## R-138

Tactile and secure cuff high visibility automotive glove.



Multi Purpose Abrasion Protection



Light Duty

## Single layer high-viz mesh with synthetic palm and touchscreen compatibility, when dexterity and flexibility matter most.

The Ringers 138 Turbo Plus glove provides flexible, lightweight protection with enhanced durability and touchscreen compatibilities for all-day automotive work.

- Developed with Ringers' F3 Technology™ and patented TPR design for superior dexterity and comfort.
- Premium synthetic leather split-palm ensures excellent grip.
- High visibility, reflective markings, and hook and loop pull tab closure provides added security on the job.



### Industries

- Oil and gas
- Automotive
- Automotive Aftermarket
- Food Processing
- Manufacturing
- Mining
- Recycling and Waste Disposal

### Applications

- General Purpose Auto Aftermarket
- Handling structural and body components
- Body painting including surface inspection
- Body panel repair and replacement
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Equipment maintenance and repair
- Delivery of parts to production line
- Vehicle Maintenance



## R-138

Tactile and secure cuff high visibility automotive glove.

### Key Features

- Secure cuff with hook and loop TPR pull tab closure
- Soft and durable premium mesh fabric on top of hand for optimal comfort and flexibility
- Premium synthetic leather used for split palm construction for long lasting durability
- Wrap around index finger protecting wear and tear zone
- Lightweight fabric between fingers for excellent dexterity
- Touchscreen compatible index, middle and thumb tips
- Reflective logo on top of hand for increased visibility

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	COLOR	PACKAGE
RINGERS R138	Cuff Style: Adjustable		8, 9, 10, 11, 12, 13	Hi Viz	5 pairs/bag, 24 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

