



MCR
SAFETY

6714FF

Memphis Harbor master

Supported / Dipped gloves

Specification Sheet

PRODUCT DESCRIPTION:

Frigid frozen fingers? No frickin' way, These foam-insulated gloves keep hands warm and dry. They are resistant to abrasions, oil, acids, chemicals and caustics.

FEATURES:

- Foam and Polar Fleece Lined
- Double Dipped PVC
- Fluorescent Orange
- Sandy Finish
- 14" Length
- Internal Knit Wrist

APPLICATIONS:

Cold storage applications, Fisheries, Transportation, Warehousing, Oil and Gas Industry



TECHNICAL DATA FOR: 6714FF

Series	Memphis Harbor master	Overall Length	14 in.
Material Group	Supported	EN 388 : CE Score - Abrasion	4
Product Type	Supported / Dipped gloves	EN 388 : CE Score - Cut	1
Glove Size	Large	EN 388 : CE Score - Tear	1
Material	PVC	EN 388 : CE Score - Puncture	2
Grade	Premium		
Insulated	Insulated		
Lining	Foam and Internal Polar Fleece		
Thumb Style	Wing		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

6714FF

Memphis Harbor master

Supported / Dipped gloves

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6714FF	Large	14.000	6.77	3.000	30.411 lb.	10.137

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved