

PU Coated 13 ga. Dyneema® (Cut/Hi-Viz)

PRODUCT DETAILS

- + 13 ga. Dyneema® shell
- + Foam polyurethane palm coating w/textured finish
- + Elastic knit wrist w/hemmed cuff



HAZARD SOLUTIONS

- Abrasion Resistant
- Cut Resistant
- Heat Resistant
- Puncture Resistant
- Tear Resistant

RATINGS

- ANSI Cut Level A3
- ANSI 2 Conductive Heat - Up to 284° F (140° C)
- EN 388 - 4443C

AVAILABLE SIZES

ITEM #	SIZE	UPC
99-1-9761-6	XS	063344256403 (6)
99-1-9761-7	S (7)	063344256434
99-1-9761-8	M	063344348559 (8)
99-1-9761-9	L (9)	063344256496
99-1-9761-10	XL	063344348498 (10)
99-1-9761-11	X2L	063344348542 (11)

*Not all styles/sizes available in all regions.

FEATURES

- 360 Degree Coverage
- Breathable
- Dexterity
- Solid Grip
- Hi-Viz

PACKAGING

- + 12 PR per Polybag 120 PR per Carton
- + Vend Pack Option Available: Yes

*Bob Dale Gloves products are tested for cut and puncture resistance. These products ARE NOT CUT AND PUNCTURE PROOF. Do not use with moving blades, tools or serrated blades.
*Not Proposition 65 compliant.