

Cantilever Shelving

Change Your Shelving As Quickly As You Change Your Mind!

Freestanding aluminum cantilever shelving for walk-in coolers eliminates the need for shelving replacements due to rusting. Units are easily adjustable and with elimination of front posts, provide 30% more storage space per shelf!

- Shelves lift-and-lock into place on uprights using locking tabs spaced on 12" centers.
- Extended front legs keep the unit stable; Fitted with an adjustable foot for easy leveling.
- Units available in 18" and 24" deep shelves (*H.D., T-Bar & Solid styles*) in multiple lengths.
- Shelving runs can be created using common center uprights (*not shown*).



6TJL7 - Cantilever Shelving



T-Bar Shelves

- **5-Year Guarantee** against material defects and workmanship.
- **Lifetime Guarantee** against rust and corrosion.

Specialty Shelving

Pot & Pan Rack: The environmentally friendly way to dry pots and pans. Unique t-bar shelf design provides maximum air circulation, with the versatility to hold smaller products and heavy loads. Equipped with four, 5" stem type swivel casters with brakes; Non-marking wheels prevent scuff marks and roll smoothly...Even on tile floors.

Keg Shelving: Built for the rigors of keg management, these units consist of two bottom, heavy duty "keg" shelves, constructed of 1½" x 2¾" x .070" wall tubing; Laterals are constructed of 1½" x 2¼" x .15" wall channel. Standard t-bar top shelf holds lighter weight product such as boxes.



Made in the USA



14G294 - Keg Shelving
NS933



14G302 - Pot & Pan Rack
PM2460

Wall-Mount Shelving provides storage for tools, supplies, and inventory. Units mount to the wall making efficient use of vertical space in supply rooms, stock rooms, garages, and other storage areas; Keeping floor spaces clear and items easily accessible and within reach. Available in a variety of sizes and styles, as well as light and heavy gauge options.



59YH22 - Inverted
97285



6TJJ8 - Vented
1122



14G290 - Solid
1125