



HEAVY-DUTY INDUSTRIAL SAFETY STRIKING & DIGGING TOOLS

EXTREME POWER DRIVE™ DEAD BLOW HAMMERS

- Shot loaded composite interior dampens striking force to reduce user fatigue
- Cast urethane face to protect hammer when striking sharp metal surfaces
- Super Grip handle is the safest in the industry, integrated ergonomic style



PART NO.	GRAINGER	WEIGHT	HANDLE LENGTH	HAMMER FACES
10063	1FC80	3 LB.	14.5"	BOTH SIDES URETHANE
10066	4GFU2	2 LB.	13.75"	URETHANE AND STEEL

STANDARD POWER DRIVE™ DEAD BLOW HAMMERS

- One piece molded non-marring face protects surface being struck
- Shot loaded composite interior dampens striking force to reduce user fatigue
- Free flowing inner shot concentrates striking power and increases driving force



PART NO.	GRAINGER	WEIGHT	HANDLE LENGTH	HAMMER FACES
10015	4A101	1 LB.	12.5"	MOLDED
10027	3MD67	2 LB.	13.75"	MOLDED AND STEEL
10025	4A102	2 LB.	13.75"	MOLDED
10035	4A103	3 LB.	14.5"	MOLDED
10045	4A104	4 LB.	15.5"	MOLDED

ERGO POWER™ SOFT SAFETY STEEL SLEDGE HAMMERS

- Softer steel reduces the risk of head “shearing” when you strike anything harder than the hammer face
- Softer Rockwell Hardness of 35RH is close to softness of brass resulting in head mushrooming and not shearing
- Heads are “BLUE” and marked with an “S” for safety and quick identification on job-site
- Very popular in the Mining industry

PART NO.	GRAINGER	WEIGHT	HANDLE LENGTH
26500	4GFD3	2 LB.	14"
26501	4GFD4	3 LB.	14"
26502	4GFD5	4 LB.	14"
26503	4GFD6	6 LB.	32"
26504	4GFD7	8 LB.	32"
26505	4GFD8	10 LB.	32"
26506	4GFD9	12 LB.	32"
26507	4GFE1	16 LB.	32"
26508	4GFE2	20 LB.	32"



CERTIFIED NON-CONDUCTIVE DIGGING TOOLS

- All Non-Conductive Digging Tools undergo 100% testing at 10,000 volts to meet/exceed IEC 60900 and ASTM F1505 standards
- Certified Non-Conductive properties combined with Nuplaglas™ and Power Pylon™ technologies provide safest/strongest tools available
- Power Pylon™ shovel blades – no shank means less breakage in the harshest applications
- Manufactured in safety orange for easy identification and electrical insulation
- Each tool carries a unique serial # permanently registered at the Nupla Corp. for traceability

TYPE OF TOOL	PART NO.	GRAINGER	GAUGE/WEIGHT	GRIP STYLE	BLADE/TIP DIMENSION	HANDLE LENGTH
ROUND POINT SHOVEL	76225	4GFE5	HD14	D GRIP	9" x 11.5"	27"
ROUND POINT SHOVEL	76245	4GFE4	HD14	BUTT GRIP	9" x 11.5"	48"
SQUARE POINT SHOVEL	76142	4GFE7	HD14	D GRIP	9.5" x 11.5"	27"
SQUARE POINT SHOVEL	76145	4GFE6	HD14	BUTT GRIP	9.5" x 11.5"	48"
PICK MATTOCK	76151	4GFF1	5 LB.	DOUBLE BIT		36"
POST HOLE DIGGER	76548	4GFF3	HD14	BUTT	6.5"	48"
POST HOLE DIGGER	76562	4GFF4	HD14	BUTT	6.5"	72"
SOIL PROBE	76401	4GFF5	2 LB.	CAP	METAL POINT	48"
SOIL PROBE	76403	4GFF6	2 LB.	CAP	METAL POINT	60"
DIGGING BAR	76292	4GFF8	6 LB.	CAP	METAL POINT	72"
DIGGING BAR	76300	4GFF9	5.5 LB.	EC	WEDGE END	48"
DIGGING BAR	76301	4GFG1	7.5 LB.	EC	WEDGE END	72"
BOLT CUTTER	76701	4GFG2	4.5 LB.	BOLT CUTTER	3" x 7" CENTER CUT	18"
BOLT CUTTER	76702	4GFG3	7.25 LB.	BOLT CUTTER	3" x 7" CENTER CUT	24"
BOLT CUTTER	76703	4GFG4	12 LB.	BOLT CUTTER	3" x 7" CENTER CUT	30"

NON-CONDUCTIVE WIRE ROPE/CABLE CUTTERS

TYPE OF TOOL	PART NO.	GRAINGER	WIRE ROPE CAPACITY	CABLE CAPACITY	CUTTING BLADE	LENGTH
ROPE/CABLE CUTTER	76450	6XF5	3/8"	1/4"	ADJ. HOLD & LOCK SHEER CUT	24"
ROPE/CABLE CUTTER	76451	6XF6	1/2"	3/8"	ADJ. HOLD & LOCK SHEER CUT	30"
ROPE/CABLE CUTTER	76452	6XF7	9/16"	7/16"	ADJ. HOLD & LOCK SHEER CUT	36"



ALL NUPLA PRODUCTS ARE WARRANTED AGAINST ANY AND ALL DEFECTS IN MATERIAL OR MANUFACTURING.

AVAILABLE THROUGH

GRAINGER®

FOR MORE INFORMATION CONTACT YOUR GRAINGER REPRESENTATIVE.

FOR THE ONES WHO GET IT DONE