



# 78 03 125

## Electronic Super Knips®



- precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- ground, very sharp cutting edges without bevel for flush cutting
- precision shaped tips cut wires resting on a board from 0.2 mm dia.
- joint with stainless steel rivet
- cutting edges additionally induction hardened
- extremely smooth movement for minimum operator fatigue
- with opening spring and opening limiter
- in INOX or special tool steel
- INOX - stainless steel
- cutting edge hardness approx. 54 HRC

Article No.	78 03 125
EAN	4003773035381
Head	polished
Handles	with multi-component grips
Style	0
Pliers	
medium hard wire Ø mm	1,0
soft wire Ø mm	0,2 - 1,6
D mm	7,5
B mm	9,0
A mm	13,5
Length mm	125
Net weight g	56



technical change and errors excepted

