

# 97 52 08

## Crimping Pliers also for two-hand operation



- for solder-free electrical connections
- the ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers
- repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- two-hand operation for easy crimping of large conductor diameters
- easy handling as a result of well balanced centre of gravity, angled head and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened

<b>Article No.</b>	97 52 08
<b>EAN</b>	4003773025481
<b>Pliers</b>	burnished
<b>Handles</b>	with non-slip plastic grips
<b>Applications</b>	End Sleeves (ferrules)
<b>Capacity mm<sup>2</sup></b>	0,25 - 6,0
<b>Number of crimping positions</b>	5
<b>AWG</b>	23 - 10
<b>Length mm</b>	250
<b>Net weight g</b>	565



First step: move the handle with two fingers only until both jaws touch the connector to be crimped



Second step: now use the whole hand for further crimping procedure



Third step: when greater hand force is required, such as e.g. when crimping insulated connectors 6.0 mm<sup>2</sup>, two-hand operation is possible by the longer handles

technical change and errors excepted



### Spare Parts

Article No.	EAN	
97 59 20	4003773053934	Extension spring for 97 52 xx
97 59 21	4003773053941	Extension spring for 97 52 xx