



MCR
SAFETY

Stratos

Safety Glasses

Value Series

Specification Sheet

PRODUCT DESCRIPTION:

The Stratos® features a one piece polycarbonate lens and a stylish wrap-around design that offers the user a wide area of protection. Integral side shields offer protection from particles entering the eyewear from the sides. The Stratos® provides an exceptional wide angle of unrestricted vision allowing you to safely assess your environment. The molded-in nose bridge comfortably fits a wide variety of faces.



FEATURES:

- Cost efficient single lens design
- Spatula temple with extendable adjustment
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays

TECHNICAL DATA FOR: SS110

Series	Stratos	ANSI Z87+	Yes
Category	Safety Glasses	CAN/CSA Z94.3	Yes
Scratch Resistant	Yes	CE EN166	Yes
Frame Material	Nylon		
Packaging	White Inner Box		
Case Pack	144 pair	Case Weight	16.119 oz.
Case Dimensions	22.047 x 14.173 x 12.992	Made In	Taiwan

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
SS010	Clear	Uncoated	No	90	Black	Black	N/A
SS110	Clear	Duramass Hard Coat	Yes	90	Black	Black	N/A
SS110AF	Clear	Duramass Anti-Fog	Yes	90	Black	Black	N/A
SS112	Gray	Duramass Hard Coat	Yes	13	Black	Black	N/A
SS120	Clear	Duramass Hard Coat	Yes	90	Blue	Blue	N/A

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

Stratos

Safety Glasses

Value Series

Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
SS130	Clear	Duramass Hard Coat	Yes	90	Blue	Red / White	N/A

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved