

AkroBin® Color Availability Guide

	RED	YELLOW	BLUE	STONE	GREEN	CLEAR	BLACK	LIGHT BLUE	PURPLE	WHITE
30210	2W072	5W869	2W776	1UGL9	2RV65	4KER2	3HRX7	5TFP9	5TFP8	12X266
30220	2W073	5W870	2W777	1UGN1	2RV66	4KER3	3HRX8	5TFR3	5TFR2	12X267
30224	2RV94	2RV98	2RV96	1UGN2	2RY10	4KER4	3HRX9	5TFR7	5TFR6	12X268
30230	2W074	5W871	2W778	1UGN3	2RV67	4KER5	3HRY1	5TFT1	5TFT0	12X269
30234	4TJ77	4TJ78	4TJ76	1UGN4	2RV68	4KER8	3HRY2	10F090	10F089	12X270
30239	5W866	5W873	5W868	1UGN6	2RV70	4KER7	3HRY4	10F094	10F093	12X272
30240	2W075	5W874	2W779	1UGN7	2RV71	4KER9	3HRY5	5TFT9	5TFT8	12X273
30265	5YM92	5YM93	5YM91	1UGP1	2RV73	4KET4	3HRZ2			
30235	5W865	5W872	5W867	1UGN5	2RV69	4KER6	3HRY3	5TFT5	5TFT4	12X271
30260	1UGP8	1UGP9	1UGR1	1UGR2	1UGR3	4KET3	3HRZ7			
30255	2RV86	2RV88	2RV90	1UGN9	2RV92	4KET2	3HRY9			
30250	2W076	5W875	2W780	1UGN8	2RV72	4KET1	3HRY7	5TFV3	5TFV2	12X274
30270	5YM95	5YM96	5YM94	1UGP2	2RV74	4KET5	3HRZ4			
30320	1UGP3	1UGP7	1UGP4	1UGP5	1UGP6	4KET6	3HRZ6			

30210	5¾ x 4½ x 3
30220	7¾ x 4½ x 3
30224	10¾ x 4½ x 4
30230	10¾ x 5½ x 5
30234	14¾ x 5½ x 5
30239	10¾ x 8¼ x 7
30240	14¾ x 8¼ x 7

30265	18 x 8¼ x 9
30235	10¾ x 11 x 5
30260	18 x 11 x 10
30255	10¾ x 16½ x 5
30250	14¾ x 16½ x 7
30270	18 x 16½ x 11
30320	8¾ x 33 x 5

