

115 Standard Duty Loop Hanger

1150100EG



The 115 Standard Duty Loop Hanger, part of the CADDY® line of fasteners and supports from ERICO, is ideal for suspending stationary, non-insulated pipe lines, including CPVC pipes, in fire sprinkler systems. A knurled insert nut helps simplify vertical adjustments and flared edges on the base (1/2" to 4" sizes) help protect pipes from coming into contact with any sharp edges of the hanger.

Features

- Flared edges help prevent any sharp surfaces from coming into contact with the pipe (1/2" to 4" sizes)
- Retained insert nut helps ensure the loop hanger and insert nut stay together
- Recommended for the suspension of stationary non-insulated pipe lines
- Manufactured to use the minimum rod size permitted by NFPA® for fire sprinkler piping
- Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 and SP-69 (Type 10)

Product Specifications

Part Number	1150100EG
Material	Steel
Finish	Pre-galvanized
Pipe Size	1"
Outer Diameter (OD)	1.315"
Rod Size (RS)	3/8"
A	3 1/4"
B	1 3/8"
C	15/16"
Static Load (F)	300 lb
Standard Packaging Quantity	100 pc
UPC	78285641731
UNSPSC	40141725
Approvals	cULus®, FM®

