

CADDY® SUPERFIX 454 Standard Duty

454004



Features

- Recommended for the suspension of stationary non-insulated pipe lines
- Easy-to-close clamp for steel pipe and copper tube
- Unique hinged design eliminates the need to disassemble the clamp prior to installation
- Clamp can be closed with one hand, without ever turning a screw
- EPDM rubber lining for sound insulation compliance with DIN 4109
- All-steel design of the closing mechanism retains strength even when exposed to heat
- Conforms with Manufacturers Standardization Society (MSS) SP-58 and SP-69 (Type 12)
- Comes with a welded 3/8" cap nut, allowing easy attachment to threaded rod
- Has a fire rating DIN EN 13501-1:E



Product Specifications

Part Number	454004
Material	Steel, EPDM-SBR rubber
Finish	Electro-galvanized
Temperature	-58 to 230 °F
Outer Diameter (OD)	0.827" – 0.906"
Pipe Size	1/2"
Copper Tube Size	3/4"
Rod Size (RS)	3/8"
B	29/32"
Static Load (F)	180 lb
Standard Packaging Quantity	100 pc
UPC	78285659046
UNSPSC	40141725

