



HIGH PERFORMANCE INDUSTRIAL MARKERS



DURA-INK® 25

The DURA-INK 25 permanent ink marker's large, chisel tip offers the flexibility of producing fine or broad marks on almost any surface. With an extra-large ink supply and metal barrel, this marker offers longer marking life and durability.

FIND A PART NUMBER:



[Reset Selections](#)

FEATURES & BENEFITS:

The versatile chisel tip can make both fine or broad marks for flexible marking needs

Smear- and water-resistant industrial ink allows for long-lasting marks

Heavy-duty metal barrel contains extra-large ink supply for longer marking life

Clip-cap stores easily in pockets and prevents rolling on surfaces

For low corrosion (low chlorides/halogens) applications, see [DURA-INK 25- Low Corrosion Color](#)

Xylene-free ink eliminates health concerns

Mark size: 1/8" or 1/4" (3 mm or 6 mm)

INDUSTRY USES:

Industrial manufacturing

Construction

Shipping supply

Automotive and other transportation

Steel mills and warehouses

Agriculture industry

Heating, ventilating, and air conditioning industry

Plumbing industry

Aviation and aerospace

SURFACE USES:

Metal

Cardboard

Pipes and tubes

Plastic

Glass

Lumber and timber

Paper

Sheet metal

MARK SIZES:

1/8" (3 mm)

1/4" (6 mm)

DETAILS:

96222 Red

96223 Black



[DURA-INK® Permanent Marker Product Bulletin](#)



[DURA-INK® 25 MSDS North America](#)



[DURA-INK® 25 European International Articles Letter](#)