

# DY35 & DY50 FOLDING CHAIR TRUCK

**BIFMA**  
INTERNATIONAL

**ANSI**

products meet  
or exceed applicable  
ANSI/BIFMA standards



## SPECS:

- 7-gauge steel bed
- Heavy-duty caster features 325lb. weight capacity; 2 swivel and 2 stationary
- DY50 has extra swivel caster in the middle for support
- 3 tubular handles-one at each end and one in the middle
- Dark Brown Powder Coated Steel
- Optional Understage Conversion Kit to store chairs in a horizontal fashion underneath stages
- 25.5" Height capacity with chairs loaded



Chair Truck Model #	Chair Model #	# of Chairs Per Truck
DY35	50,100,200,300,1200,1300,2200,2300,800	35
DY35	3200	24
DY35	602	28
DY35	1000,1100	30
DY50	50,100,200,300,1200,1300,2200,2300,800	50
DY50	3200	35
DY50	602	40
DY50	1000,1100	42

## DIMENSIONS:


**DY35 OVERALL: 38 1/2"H X 19 1/4"W X 81"D**

**DY50 OVERALL: 38 1/2"H X 19 1/4"W X 109 1/2"D**

**INSIDE WIDTH: 19"W WITH A 2" LIP TO ACCOMMODATE CHAIRS 15 1/4"W - 19"W**

FRAME COLOR  
#84 DARK BROWN

#DY50



#DY35



**National Public SEATING Corp.**

800.261.4112 | www.NationalPublicSeating.com