

18", 20", 24" & 30" Quiet Plus Pedestal & Wall Mount Fans



HVAC/R fact sheet



Pedestals



Wall Mounts

Quiet Plus Pedestal & Wall Mount Fan

The 2WC and 4PR Series Quiet Plus Fan is designed for heavy duty and is energy efficient with the lowest watts per CFM. The ultra quiet die cast aluminum airfoil propeller is excellent for churches, schools, industrial and commercial applications. Features include:

- 1/5 or 1/3 HP, 115V, 3 Speed, 1 Phase, Totally Enclosed Ball Bearing Motor
- Patented Modular Motor End Dome for easy maintenance
- 15 Ft. Power Cord with Plug
- Meet OSHA standards
- UL/CUL listed

SKU NO.	CFM		HP	Propeller Dia. (in.)	MOTOR RPM			Volts	Amps
	Low / Med / High				Low / Med / High				
Quiet Plus Non-Oscillating Pedestal Fans									
4PRW3	1805/2113/2600		1/5	18	780/915/1125	115	1.41		
4PRV8	1657/2060/3100		1/5	20	600/745/1120	115	1.65		
2WCG4	3325/4556/5588		1/3	24	700/900/1110	115	2.50		
2WCF9	4463/6259/8402		1/3	30	660/880/1098	115	2.60		
Quiet Plus Non-Oscillating Wall Mount Fans									
4PRW4	1805/2113/2600		1/5	18	780/915/1125	115	1.41		
4PRV9	1657/2060/3100		1/5	20	600/745/1120	115	1.65		
2WCG5	3325/4556/5588		1/3	24	700/900/1110	115	2.50		
2WCG1	4463/6259/8402		1/3	30	660/880/1098	115	2.60		
Quiet Plus Oscillating Pedestal Fans									
4PRW1	1805/2113/2600		1/5	18	780/915/1125	115	1.41		
4PRV6	1657/2060/3100		1/5	20	600/745/1120	115	1.65		
2WCG6	3125/4356/5387		1/3	24	628/850/1070	115	2.50		
2WCG2	4063/5859/7996		1/3	30	561/789/1045	115	2.90		
Quiet Plus Oscillating Wall Mount Fans									
4PRW2	1805/2113/2600		1/5	18	780/915/1125	115	1.41		
4PRV7	1657/2060/3100		1/5	20	600/745/1120	115	1.65		
2WCG7	3125/4356/5387		1/3	24	628/850/1070	115	2.50		
2WCG3	4063/5859/7996		1/3	30	561/789/1045	115	2.90		

Exclusively from Grainger.

Call or visit your local branch or go to grainger.com/dayton for complete product line information