

# YES!

WE CAN!

# DURATOUGH™

## Classic and Galvanite™ Series All-Welded Cabinets

**Classic Series** cabinets are fabricated from prime grade cold rolled sheet steel.

**Galvanite Series** cabinets are fabricated from galvanized sheet steel which has a zinc-iron alloy coating that is applied at the mill providing protection against high-humidity and moist environments. This coating also prevents corrosion from spreading when the paint and/or coating is scratched away.

**Heavy-Duty cabinets** are fabricated from 16 gauge sheet steel and are fully-welded creating a rigid, durable unit.

**Extra Heavy-Duty cabinets** are fabricated from 14 gauge steel which is 25% thicker than 16 gauge providing MAXIMUM durability.

**Safety-View® Series cabinets** incorporate polycarbonate panels in both doors of our extra heavy-duty Classic Series cabinets allowing contents to be visible without compromising security.

**Ventilated Series cabinets** are fabricated to the same rugged standards as our extra heavy-duty Classic Series cabinets with the added benefit of being fully ventilated with diamond perforated doors and sides and a 13 gauge flattened expanded metal back.

COLOR  
SELECTION

738  
CHARCOAL  
(CL)



42" High Storage Cabinet



60" High Storage Cabinet



78" High Storage Cabinet



**Standard Features for all DuraTough™ Classic and Galvanite™ Series Cabinets**

- All-welded construction
- Double door design
- Solid doors are reinforced with an 18 gauge full-height door stiffener providing a rigid torque-free door.
- 3-point turn handle locking using 3/8" diameter locking rods operated by a 3/16" gauge steel handle. Handle is painted to match cabinet.
- Heavy-duty 13 gauge 7-knuckle 3-1/2" butt hinges welded to door and securely riveted to frame.
  - Solid sides are formed to be integral with vertical door frame.
  - Top is formed to be integral with horizontal top door frame.
  - Bottom is formed to be integral with horizontal bottom door frame and includes double return bends at all four sides maximizing unit rigidity.

- Back is welded to cabinet top, bottom and sides
- Shelves are formed to provide maximum capacity and are adjustable on 3" centers. Shelves bolt to shelf support channels which are welded to sides.
  - 78" high storage cabinets include 4-adjustable shelves
  - 60" high storage cabinets include 3-adjustable shelves
  - 42" high storage cabinets include 2-adjustable shelves
  - 78" high combination cabinets include one full-width upper shelf, a center partition, 3 partial-width shelves and one partial-width coat rod
- Optional leg kits are available and can be bolted on to all DuraTough cabinets.
- Color: 738 Charcoal



18-gauge full-height door stiffener provides maximum rigidity to both doors



Heavy-Duty 3/16" thick steel handle with padlock hasp.



1/8" thick latch and 3/8" diameter lock rods insure maximum security



Combination Cabinet



Safety-View Cabinet



Ventilated Cabinet

# YES!

**WE CAN!**



## DuraTough™ Classic Series

Catalog Number	Type	Width (In)	Depth (In)	Height (In)	No. of Shelves
<b>HEAVY-DUTY-16 GAUGE</b>					
1YHD9	Storage	36	21	42	2
1YHE1	Storage	36	21	60	3
1YHE2	Storage	36	21	78	4
1YHE3	Storage	36	24	78	4
1YHE4	Storage	48	24	60	3
1YHE5	Storage	48	24	78	4
1YHE6	Storage	60	24	78	4
1YHE7	Combination	36	24	78	4
1YHE8	Combination	48	24	78	4
1YHE9	Combination	60	24	78	4
<b>ADDITIONAL SHELVES, HEAVY-DUTY-16 GAUGE</b>					
1YHF1	Shelf	36	21	----	1
1YHF2	Shelf	36	24	----	1
1YHF3	Shelf	48	24	----	1
<b>EXTRA HEAVY-DUTY-14 GAUGE</b>					
1YHF4	Storage	36	21	42	2
1YHF5	Storage	36	21	60	3
1YHF6	Storage	36	21	78	4
1YHF7	Storage	36	24	78	4
1YHF8	Storage	48	24	60	3
1YHF9	Storage	48	24	78	4
1YHG1	Storage	60	24	78	4
1YHG2	Combination	36	24	78	4
1YHG3	Combination	48	24	78	4
1YHG4	Combination	60	24	78	4
<b>ADDITIONAL SHELVES, EXTRA HEAVY-DUTY-14 GAUGE</b>					
1YHG6	Shelf	36	21	----	1
1YHG7	Shelf	36	24	----	1
1YHG8	Shelf	48	24	----	1

## DuraTough™ Ventilated

Catalog No	Type	Width (In)	Depth (In)	Height (In)	No. of Shelves
34A493	Storage	36	24	78	4
34A494	Storage	48	24	78	4

## DuraTough™ Safety-View™

34A495	Storage	36	24	78	4
34A496	Storage	48	24	78	4

## CORROSION RESISTANT

## DuraTough™ Galvanite Series

Catalog Number	Type	Width (In)	Depth (In)	Height (In)	No. of Shelves
<b>HEAVY-DUTY-16 GAUGE</b>					
1YHH1	Storage	36	21	42	2
1YHH2	Storage	36	21	60	3
1YHH3	Storage	36	21	78	4
1YHH4	Storage	36	24	78	4
1YHH5	Storage	48	24	60	3
1YHH6	Storage	48	24	78	4
1YHH7	Storage	60	24	78	4
1YHH8	Combination	36	24	78	4
1YHH9	Combination	48	24	78	4
1YHJ1	Combination	60	24	78	4
<b>ADDITIONAL SHELVES, HEAVY-DUTY-16 GAUGE</b>					
1YHJ2	Shelf	36	21	----	1
1YHJ3	Shelf	36	24	----	1
1YHJ4	Shelf	48	24	----	1
<b>EXTRA HEAVY-DUTY-14 GAUGE</b>					
1YHJ5	Storage	36	21	42	2
1YHJ6	Storage	36	21	60	3
1YHJ7	Storage	36	21	78	4
1YHJ8	Storage	36	24	78	4
1YHJ9	Storage	48	24	60	3
1YHK1	Storage	48	24	78	4
1YHK2	Storage	60	24	78	4
1YHK3	Combination	36	24	78	4
1YHK4	Combination	48	24	78	4
1YHK5	Combination	60	24	78	4
<b>ADDITIONAL SHELVES, EXTRA HEAVY-DUTY-14 GAUGE</b>					
1YHK7	Shelf	36	21	----	1
1YHK8	Shelf	36	24	----	1
1YHK9	Shelf	48	24	----	1

## DuraTough™ Cabinet Leg Kits

Catalog No	Type	Width (In)	Depth (In)	Height (In)	Legs Per Kit
1YHG9	Leg Kit	4	21	4	2
2KEJ7	Leg Kit	4	24	4	2

Leg kits can be added to any Hallowell DuraTough Cabinet. Legs are fabricated from galvanized corrosion resistant steel and are easily bolted to cabinet bottom. Includes hardware for field attachment.

