

PG505

UTILITY PAPER MASKING TAPE

INTERTAPE POLYMER GROUP TECHNICAL DATA SHEET

DESCRIPTION

A paint contractor industry staple. Beige, smooth crepe paper masking tape coated with a pressure-sensitive natural rubber adhesive. Offers an excellent balance of quick stick, panel adhesion and holding properties. Not recommended for outdoor exposure.

PRODUCT APPLICATION

For general purpose masking.

GOVERNMENT COMPLIANCE

Government specification conformance: ASTM D6123, Type I C.I.D. A-A-883B Type 1.

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard test. The data should not be considered as specifications.

Backing	Smooth Crepe Paper
Adhesive	Natural Rubber/Resin
Adhesion to Steel (oz/in of width) PSTC-1	30 (8.2 N/25mm)
Tensile Strength (lbs/in of width) PSTC-31	20 (88 N/25mm)
Elongation (at break) PSTC-31	10%
Total Thickness (mils) PSTC-33	5.8 (0.147mm)
Quick Stick (oz/in of width) PSTC-5	
To Kraft	5 (1.4 N/25mm)
To Steel	11 (3 N/25mm)
Operating Temperature Range	+50°F ~ +200°F (+10°C ~ +93°C)
Color	Beige



3647 Cortez Road West | Bradenton, FL 34210 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 02/11

