


MODELS: K15A - 8P



JENNY PRODUCTS, INC.
850 N. Pleasant Ave.
Somerset, Pennsylvania 15501

Parts List for Model K15A-8P


NOTE: The quantity number indicates the total number of pieces required for a complete pump repair.
When ordering parts give compressor model, serial number and part number. Order assemblies when possible.

<u>REF. NO.</u>	<u>PART NO.</u>	<u>DESCRIPTION</u>	<u>QTY.</u>
1	411-1014	TANK,PORTBL,8G,NON,K&G>G,RPLMT,Gas	1
2	120-1286	PIN,COTTER,PLATED,3/16 DIA X2 LONG	2
3	150-1218	AXLE,STEEL,PLATED,8P,5/8"DIA X5" LONG	1
4	150-1219	WHEEL,PNEUM,410/350X4,4"CNTRD,5/8"ID	1
5	104-1249	PAD,RUBBER,40D,11GA,1-1/4X1-7/8X2-1/2,WP	4
6	141-1058	DRAIN,PETCOCK,BRASS,1/4"NPTM,DC14	2
7	104-1072	GRIP,HANDLE,RUBBER,YELLOW,7/8",STERILE	2
8	104-1001	HOSE,AIR,200 PSI,3/8"ID X18" LONG	1
9	104-1075	CAP,COVER,PLASTIC,RED,0.40 X 1/4" X 3/8"	2
10	120-1173	CLAMP,HOSE,GEAR,WORM,SS,5/16" TO 7/8"	2
11	121-1145	BARB,HOSE,ELBOW,MALE,BRASS,3/8HSX3/8NPTM	2
12	160-1001	REGULATOR,PRESSURE,AIR,3/8"NPT	1
13	150-1083	BRACKET,REGULATOR,STEEL,PLATED,3/8",BR	1
14	120-1243	SCREW,FLANGE,HEX,SERR,ST,PL,1/4-20 X 1/2	2
15	120-1116	NUT,LOCK,FLANGE,HEX,SERR,ST,PLTD,1/4-20	4
16	142-1003	GAUGE,PSI,200#,BK MT,JENNY,1.5,1/4",PG14	2
17	141-1047	VALVE,PILOT,W/HAND UNLOADER,125PSI,1/4"M	1
18	122-1145	NIPPLE,STEEL,SCH 80,PLTD,1/2" X 1-1/2" L	1
19	141-1004	VALVE,SAFETY,ASME,1/4",165 PSI,54 SCFM	1
20	150-1121	BLOCK,MANIFOLD,ZINC,5 HOLE,TAPPED,MC-5	1
21	121-1025	CONNECTOR,MALE,COMPRESSION,BR,1/4TBX1/8"	1
22	121-1137	TUBING,COPPER,PRE-CUT,1/4"X20-1/2" LONG	1
23	121-1008	CONNECTOR,MALE,BRASS,5/8-45SAEX1/2"NPTM	1

Parts List for Model K15A-8P

NOTE: The quantity number indicates the total number of pieces required for a complete pump repair.
When ordering parts give compressor model, serial number and part number. Order assemblies when possible.

<u>REF. NO.</u>	<u>PART NO.</u>	<u>DESCRIPTION</u>	<u>QTY.</u>
24	122-1032	NIPPLE,STEEL,SCH 40,1/4" X 3" L	1
25	122-1083	CAP,HEX,STEEL,1/4"NPT	1
26	421-1102	PUMP,CMPSR,PISTON,REPLCMT,BLUE,KU	1
27	120-1009	SCREW,CAP,HEXHD,GR5,ST,PLTD,1/4-20X1-1/4	4
28	120-1070	WASHER,FLAT,STEEL,PLATED,SAE,1/4"	4
29	120-1116	NUT,LOCK,FLANGE,HEX,SERR,ST,PLTD,1/4-20	4
30	150-1105	FILTER,AIR,2PC,W/SILENCER&FILTER,G154	1
31	360-1392	AFTERCOOLER,HOSE,SS,TEFLON,5/8"ODX19"L	1
32	121-1032	ELBOW,MALE,COMPRESSION,BR,1/4TBX1/8"NPTM	1
33	120-1267	SCREW,PAN HD,PHIL,STEEL,PLTD,1/4-20 X 1"	3
34	120-1072	WASHER,FENDER,ST,PLATED,1/4"X1-1/2"OD	1
35	120-1177	SCREW,SELF DRILL,HEX,ST,PL,12 X 3/4	6
36	150-1217	BELTGUARD K GAS & ELECTRICAL NEW 2-1-05	1
37	120-1119	NUT,LOCK,FLANGE,HEX,SERR,ST,PLTD,5/16-18	6
38	120-1075	WASHER,FLAT,STEEL,PLATED,5/16"	4
39	154-4L470	BELT,VEE,A45,4L-470	1.5 Hp 1
40	120-1108	KEY,STEEL,BLACK,3/16X3/16X 1-1/2" LENGTH	1
41	154-1204	PULLEY,CI,SG,5.0PDA,5/8ID,AK54X5/8	1.5 Hp 1
42	130-1014	MOTOR,1.5HP,115-230/60/1,1725RPM,ODP	1
43	120-1018	SCREW,FLANGE,HEX,SERR,ST,PLD,5/16-18X3/4	4
44	123-1029	CONNECTOR,ROMEX,CLAMP,STRAIGHT,3/8"	1
45	123-1023-01	CORD,DROP,SJOW,5-15PLUG,15 AMP,12/3,6 FT	1



MODEL K & KU
Two Cylinder Single Stage
2-1/2" Bore X 2" Stroke

JENNY PRODUCTS, INC.
850 N. Pleasant Ave.
Somerset, Pennsylvania 15501

Parts List for Model K & KU

NOTE: The quantity number indicates the total number of pieces required for a complete pump repair.
When ordering parts give compressor model, serial number and part number. Order assemblies when possible.

<u>REF. NO.</u>	<u>PART NO.</u>	<u>DESCRIPTION</u>	<u>QTY.</u>
1	120-1163	PIN,ROLLED,COILED,STL,BLK,1/4ODX1L,K25	1
2	220-1093	FLYWHEEL,K PUMP,CI,10-3/8,1 GROOVE,K23A	1
2A	220-1090	FLYWHEEL,GT PUMP,CI,13-1/4,2 GROOVE,G23 MODEL KC ONLY (INCLUDES #20)	1
3	150-1036	SEAL,OIL,LIP,SINGLE,0.875 DIA,K11E	1
4	220-1009	CRANKCASE,K PUMP,CI,MACHINED,K1	1
5	122-1032	NIPPLE,STEEL,SCH 40,1/4" X 3" L	1
6	122-1083	CAP,HEX,STEEL,1/4"NPT	1
7	150-1000	BEARING,BALL,K9	2
8	220-1010	CRANKSHAFT,K PUMP,CI,MACHINED,K20A	1
9	104-1000-01	GASKET,CAP,BEARING,F&K&G PUMP,1/32THK,L3 104-1000-01 is the stock bearing cap gasket	1
10	104-1000-02	GASKET,CAP,BEARING,F&K&G PUMP,1/64THK,L4 104-1000-02 are spacers to adjust crankshaft end play	1
11	220-1001	CAP,BEARING,K PUMP,CI,MACHINED,K2	1
12	120-1002	SCREW,CAP,HEXHD,GR5,ST,BLK,1/4-20X5/8 (10FT-LB.)	4
13	610-1029	PLUG,CRANKCASE,FILL,OIL INCLUDES #14	1
14	104-1016	RING,O,BUNA-N,5/8"IDX13/16"ODX3/32"THK	1
15	310-1001-01	ROD,CONNECTING,ALUM,MACHINED,L21L&L21K	2
16	120-1068	WASHER,LOCK,SPLIT,ST,BLK,HIGH CLLR,1/4"	4
17	610-1047	SCREW,ROD,STEEL,W/LOCK WASHER,1/4-20,L22 (10 FT - LB.)	4
18	104-1103	BUMPER,WRIST PIN,PLASTIC,K36A	4
19	150-1005	PIN,PISTON,STEEL,HARDENED,K35	2
20	220-1005	PISTON,PUMP,ALUMINUM,MACHINED,K32	2

Parts List for Model K & KU

NOTE: The quantity number indicates the total number of pieces required for a complete pump repair.
When ordering parts give compressor model, serial number and part number. Order assemblies when possible.

<u>REF. NO.</u>	<u>PART NO.</u>	<u>DESCRIPTION</u>	<u>QTY.</u>
21	610-1065	KIT,RING,OIL,W/EXPANDER,ASSY,K34	2
22	150-1003	RING,COMPRESSION,PISTON,STEEL,EBA 22,K33	4
23	120-1162	GROOVE PIN #7X1/2 GDS-RH-HD,K18	1
24	104-1019	RETAINER,BREATHER,CRANKCASE,PLASTIC,K17	1
25	104-1189	SEAL,BREATHER,CRANKCASE,RUBBER,K16	1
26	104-1006	GASKET,CYLINDER,K&G&W PUMP,1/32THK,K31	1
27	120-1017	SCREW,CAP,HEXHD,GR5,ST,BLK,5/16-18X3/4 (15FT-LB.)	6
28	360-1150	CYLINDER K30 BLUE EMGLO REPLACEMENT	1
29	104-1007	GASKET,PLATE,VALVE,K&G&W PUMP,1/32TK,L41	1
30	150-1041	RETAINER,VALVE,STEEL,PAS,0.062"THK,K43	4
31	109-1010	VALVE,CHECK,BUMPER,STEEL,K44	4
32	150-1017	SPRING,CONE,SS,VALVE,INTAKE,K45	2
33	109-1011	VALVE,DISC,STEEL,K47	4
34	150-1018	SPRING,CONE,SS,VALVE,DISCHARGE,K46	2
35	104-1008	GASKET,HEAD,K&G&W PUMP,1/32THK,L51	1
36	220-1013	PLATE,VALVE,L PUMP,CI,MACHINED,L40	1
37	310-1004	HEAD,START/STOP,G PUMP,REPLACEMNT,L50	1
38	120-1252	BOLT,STUD,HEX,ST,5/16-18X2-1/4X5/8,K52-1 (22FT - LB.)	2
39	120-1028	SCREW,CAP,HEXHD,GR5,ST,BLK,5/16-18X2-1/4 (TORQUE TO 22 FT - LB.)	4
40	320-1121	FILTER,W/DECALS,ASSY,G154S	1
41	150-1104	ELEMENT,FILTER,AIR,G54E	1
42	220-1016	HEAD,UNLOADING,G PUMP,CI,6HOLES,LU80	1

Parts List for Model K & KU

NOTE: The quantity number indicates the total number of pieces required for a complete pump repair.
When ordering parts give compressor model, serial number and part number. Order assemblies when possible.

<u>REF. NO.</u>	<u>PART NO.</u>	<u>DESCRIPTION</u>	<u>QTY.</u>
43	150-1020	SPRING,VALVE,UNLOADER,INTAKE, KU83	2
44	104-1020	RING,O,SILICON,7/16"IDX5/8"ODX3/32"THK	2
45	150-1028	PISTON,UNLOADER,VALVE,CHECK,BRASS,KU81	2
46	104-1015	RING,O,BUNA-N,1/2"IDX11/16"ODX3/32"THK	2
47	122-1051	PLUG,HEX ,BRASS,11/16-16 UN-2B X .550	2
48	121-1032	ELBOW,MALE,COMPRESSION,BR,1/4TBX1/8"NPTM	1

ASSEMBLIES

49*	610-1042	VALVE,UNLOADER,HEAD,PUMP,ASSY INCLUDES 43, 44, 45, 46, 47	2
49**	610-1042	VALVE,UNLOADER,HEAD,PUMP,ASSY 150-1042 (2pcs) 120-1167 (2pcs) must be ordered extra	2
50	610-1031	VALVE,CHECK,SUCTION,ASSY INCLUDES 30, 31, 32, 33	2
51	610-1020	KIT,PUMP,RING,PISTON,F&K&G&W PUMP INCLUDES 22 (4), AND 21 (2),	1
52	610-1027	VALVE,BREATHER,CRANKCASE,K PUMP,ASY INCLUDES 23, 24, 25	1
53	610-1032	VALVE,CHECK,DISCHARGE,ASSY INCLUDES 1 EACH 30, 31, 33, 34	2
54	610-1026	KIT,GASKET,K PUMP,ASSY INCLUDES 9, 10, 26, 29, 35	1
55	610-1122	KIT,BASIC,REPAIR,K PUMP W / FILTER INCLUDES 50 (2), 51 (2), 52, 53 (2), 54, 150-1010 FILTER	1
56	610-1304	KIT,BASIC,REPAIR,KU PUMP,W / FILTER INCLUDES 41 FILTER, 49 (2), 50 (2), 51 (2), 52, 53 (2), 54	1
57	610-1123	KIT,BASIC,REPAIR,KU PUMP W / FILTER INCLUDES 50 (2), 51, 52 (2), 53 (2), 54, 150-1010 FILTER	1
58	610-1028	PISTON,W/RINGS&PIN,ASSY INCLUDES 18 (2), 19, 20, 21, 22 (2)	2

Parts List for Model K & KU

NOTE: The quantity number indicates the total number of pieces required for a complete pump repair.
When ordering parts give compressor model, serial number and part number. Order assemblies when possible.

<u>REF. NO.</u>	<u>PART NO.</u>	<u>DESCRIPTION</u>	<u>QTY.</u>
59	610-1045	PLATE,VALVE,W/VALVES,ASSY INCLUDES 30 (4), 31 (4), 32 (2), 33 (4), 34 (2) AND 36 INSTALLED INCLUDING 29 AND 35	1
60	310-1008	HEAD,UNLOADING,K&G,W/1/2"PRT 6 HLE INCLUDES 42 W/UNLOADER 49, (2) SETS OF 49	1
49* for units built after serial #D110105001			1
49** for units built before serial #D103105001			1