

A19

# Temperature Control with Rainproof Enclosure

## Description

This is a remote bulb temperature control with a rainproof (NEMA Type 3R) enclosure.

## Features

This control has a rainproof gasketed enclosure.

## Applications

Use for control of cooling tower sump heaters.



**A19ANC-1**

## Selection Chart

Code Number	Switch Action	Range °F (°C)	Diff F° (C°)	Bulb and Capillary	Bulb Well No. (order separately)	Range Adjuster	Max. Bulb Temp. °F (°C)
A19ANC-1C	SPDT	0 to 150 (-18 to 66)	5 (2.8) Fixed	0.290 x 2 1/2 in. 10 ft. Cap.	WEL11A-601R	Screwdriver slot	190 (88)

## Technical Specifications

- maximum bulb temperature: 190°F (88°C)
- maximum ambient temperature: 140°F (60°C)

## Electrical Ratings

Motor Ratings VAC		120	208	240	277
AC Full Load A		16.0	9.2	8.0	—
AC Locked Rotor A		96.0	55.2	48.0	—
Non-Inductive A	When connected SPST	22.0	22.0	22.0	22.0
	When connected SPDT	16.0	9.2	8.0	6.9
Pilot Duty – 125 VA, 24 to 600 VAC					