

# Markal®

## HIGH PERFORMANCE INDUSTRIAL MARKERS



### B® PAINTSTIK®

---

As Markal's most versatile and economic marker, the original B Paintstik solid paint marker combines the durability of paint in the convenience of a crayon. The real paint formula has superior marking performance on oily, icy, wet, dry or cold surfaces and is weather- and UV-resistant. This Paintstik works on rough, rusty, smooth, or dirty surfaces.



---

## FEATURES & BENEFITS:

Real paint for long-lasting, highly visible marks

Superior marking on rough, rusty, or dirty surfaces

Solid paint marker eliminates replacement tips, sharpening or priming, increasing productivity

Easy-to-hold, recyclable paperboard holder protects Paintstik for maximum use

Weather- and UV-resistant for long-lasting marks

For low corrosion (low chlorides/halogens) applications, see **[B Paintstik - Low Corrosion Colors](#)**

Offered in 3 sizes: standard 11/16" (17 mm), fine 3/8" (9.5 mm), and king size 1" (25.4 mm)

Marking range: -50°F to 150°F (-46°C to 66°C)

Made in U.S.A.

---

## INDUSTRY USES:

Steel mills and warehouses

Forge and casting foundries

Ship building and repair

Metal fabrication

Tire repair and retreading

Lumber and timber industry

Construction

---

## SURFACE USES:

Steel and iron

Pipes and tubes

Rubber and tires

Lumber and timber

Plastic

Glass□

**DETAILS:**

80220 White  
80221 Yellow  
80222 Red  
80223 Black  
80224 Orange  
80225 Blue

---

80226 Green  
80227 Pink  
80228 Purple  
80229 Brown  
80230 Gray  
80231 Gold

---

80232 Aluminum  
82821 Fluorescent Yellow  
80420 White Fine Size  
80421 Yellow Fine Size  
80260 White King Size  
80250 White Hex Size  
80251 Yellow Hex Size

---



[B® Paintstik® Product Bulletin](#)



[B® Paintstik® MSDS North America](#)



[B® Paintstik® European International Articles Letter](#)