

Markal®

HIGH PERFORMANCE INDUSTRIAL MARKERS



PRO-LINE®

The PRO-LINE Fine and Micro liquid paint markers combine the durability of paint with the marking precision of fine, valve-actuated tips. Whether marking on small surface areas or where easily-readable marks are required, the small tip sizes provide highly-visible, sharp lines for greater mark identification.



FEATURES & BENEFITS:

Available in fine and micro tip sizes for precise, permanent paint marking

Offered in 2 sizes: fine 1/16" (1.5 mm) and micro 1/32" (1 mm)

High-strength, lightweight barrel designed for industrial-grade use

Self-storing cap with clip protects tip for longer life and stores easily in pocket

Xylene-free paint reduces user health risks and eliminates California Proposition 65, EPA HAPS and SARA 313 concerns in the U.S.A.

Marking range: 0°F to 150°F (-18°C to 66°C)

INDUSTRY USES:

Industrial manufacturing

Welding

Automotive and other transportation

Metal fabrication

Textile industry

SURFACE USES:

Steel and iron

Cloth and fabric (textiles)

Plastic

Glass

Pipes and tubes

MARK SIZES:

1/16" (1.5 mm)

1/32" (1 mm)



DETAILS:

96871 White - Fine
96872 Yellow - Fine
96873 Black - Fine
96874 Red - Fine

96875 Blue - Fine
96876 Green - Fine
96877 Orange - Fine
96879 Light Green - Fine

96888 White - Micro
96889 Yellow - Micro
96890 Black - Micro
96891 Red - Micro



[PRO-LINE® Fine and Micro Product Bulletin](#)



[PRO-LINE® MSDS North America](#)



[PRO-LINE® Fine European International Articles Letter](#)



[PRO-LINE® Micro European International Articles Letter](#)