



PRO-LINE® WP

The PRO-LINE WP is a liquid paint marker engineered for enhanced marking performance and adhesion on wet surfaces. The fast-drying formula resists spreading and running when in contact with water or water-based fluids to leave a bright, permanent mark.



FEATURES & BENEFITS:

Specially formulated paint resists running or spreading on wet or damp surfaces to leave permanent, highly-visible marks

Xylene-free paint reduces user health risks and eliminates California Proposition 65, EPA HAPS and SARA 313 concerns in the U.S.A.

Low in V.O.C.'s and will not contribute to ground-level ozone

Metal barrel and fiber tip provide durability for longer marking life

Marking range: -50°F to 150°F (-46°C to 66°C)

Made in U.S.A.

INDUSTRY USES:

Machining shops

Stamping works

Plasma cutting

Metal fabrication

Ship building and repair

Oil and gas

High-humidity climates

Aviation and aerospace

SURFACE USES:

Steel and iron

Aluminum

Pipes and tubes

Plastic

Glass

Rubber

Ceramic

MARK SIZE:

1/8" (3 mm)



DETAILS:

96930 White
96931 Yellow
96932 Red

96933 Black
96934 Blue
96935 Green

96936 Orange
96937 Silver



[PRO-LINE® WP Product Bulletin](#)



[PRO-LINE® WP MSDS North America](#)



[PRO-LINE® WP European International Articles Letter](#)