

# Nashua<sup>®</sup> 307

## TAPE PRODUCTS Utility Grade Duct Tape

### 7 mil Polyethylene-Coated Cloth Natural Rubber-Based Adhesive

Available Colors: Silver & Black

Standard Sizes: 48mm x 55M, 72mm x 55M

Nashua 307 offers a tough, conformable backing that tears smoothly and without difficulty. Its' high tack natural rubber adhesive bonds well to most surfaces making it suitable for a wide range of utility applications including:

- Maintenance and general repair
- Joint sealing & pipe wrapping
- Bundling, patching & mending
- Heavy-duty box sealing
- More...



### Physical Properties

	Standard UOM	Metric UOM
<b>Total Thickness</b>	7 mils	177.8 mic
<b>Adhesion to Steel</b>	46 oz/in	5.03 N/cm
<b>Tensile Strength</b>	21 lb/in	36.78 N/cm
<b>Operating Temperature</b>	40-200°F	4-93°C
<b>VOC Content</b>	<1 g/L	



Visit our website to learn more!



For more information:  
25 Forge Parkway  
Franklin, MA 02038  
Phone 508.918.1600 • Fax 508.918.1901  
Toll Free: 1.800.343.7875

[tapes.berryplastics.com](http://tapes.berryplastics.com)

