



Maximum Thrust Minimal Effort

Efficient air gun for cleaning the heaviest debris with ease.



OSHA Safety Air Guns

All Guardair Safety Air Guns are designed with nozzles that meet or exceed OSHA STANDARD 1910.242(b) 30 psi requirement.



XtraThrust®

Guardair's XtraThrust® Series provides all the benefits of the Long John® Series but with 40% more power. Ideal for the toughest applications and to move the heaviest debris, the XtraThrust nozzle generates over 300% more thrust compared to conventional air guns, yet limits static pressure to less than 30 psi should the tip become blocked. Ergonomic, Classic+ pistol grip-style handle provides maximum user comfort.

- 54 CFM Compressed Air Usage
- 12 HP Minimum Compressor Size
- 108 dBA Noise Level
- Long Comfort Trigger



ALUMINUM

Part Number	Extension Length
75XT006AA	6"
75XT012AA*	12"
75XT018AA	18"
75XT024AA*	24"
75XT036AA*	36"
75XT048AA	48"
75XT060AA	60"
75XT072AA	72"

Lightweight to reduce operator fatigue during extended cleaning. *Available in 10 packs.



STEEL

Part Number	Extension Length
75XT012SS	12"
75XT018SS	18"
75XT024SS	24"
75XT036SS	36"
75XT048SS	48"
75XT060SS	60"
75XT072SS	72"

Heavier and more rugged than aluminum. Built for maximum durability in tough environments.



NYLON

Part Number	Extension Length
75XT018NN	18"

Insulated nylon extension and nylon nozzle protects users from electrical shock hazards and protects equipment from damage due to accidental short circuits.

FREE OSHA KIT

Test your air guns for safety.



Stay OSHA compliant and keep your team safe with our Free OSHA Compliance Kit. Test your pneumatic air guns, meet regulations, and enhance workplace safety. Order yours today!



FREE OSHA KIT