



NOTES:

1. PEX SIZE : 3/4
2. TUBE SIZE : 1
3. MAX. PRESSURE : 80 psi
4. PIPE SIZE - PIPE FITTING : 1
5. TEMP. RANGE : 33°F to 200°F
6. BASIC FITTING SHAPE: Adapter
7. TUBE FITTING MATERIAL : Low Lead Brass
8. FITTING CONNECTION TYPE : PEX x Female Swivel
9. STANDARDS : ASTM F877, ASTM F1807, CAN CSA B137.5 NSF 1 4 NSF 61

GRAINGER

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE

1.43

COMPONENT

PEX and Pipe Adapter

10A542

Adapter, Low Lead Bras, 1" Tube

UNIT

INCH

SHEET

1 of 1