



NOTES:

1. BASIC MATERIAL : Metal
2. BODY MATERIAL : Nickel Plated Brass
3. CONNECTION TYPE : Tube x Tube
4. MAX. PRESSURE : 250 psi
5. TEMP. RANGE : 0° to 160°F
6. GASKET MATERIAL : Rubber
7. SPECIAL FEATURES : Universal Thread System Compatible with Inch and Metric Thread

GRAINGER
 100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.97

COMPONENT	Elbow, 90°	
UNIT	MM	
SHEET	1 of 1	
1WUX2	Union Elbow,90 Deg,10mm Tube Sz,PK3	