




Series	H	Shut Off	Yes
Sleeve Material	316 Stainless Steel	Valve Design	Poppet
Connection Type	MNPT	Seal Material	Viton
Coupler Body Size	1/4"	Max. Pressure	5000 psi
Coupler Flow Rate	3.8 gpm	Coupler Finish	Plain
Coupler Thread Size	1/4"-18	Locking Mechanism	Ball
Coupler Interchange Type	H	Coupler Body Material	316 Stainless Steel



**NOTES:**

1. ITEM: Hydraulic Coupler Body
2. BEARING MATERIAL: 316 Stainless Steel
3. OPERATING TEMP. RANGE: -20° to 375°F
4. QUICK COUPLER TYPE: Hydraulic Coupler Body

COMPONENT	Hydraulic Quick Couplers
-----------	--------------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.53

**20LG76**  
 Coupler Body, 1/4-18, Body, 316 SS

UNIT  
 INCH  
 SHEET  
 1 of 1