






NOTES:

1. MATERIAL : Alloy Steel
2. FINISH : Zinc Plated
3. THREAD TYPE : Coarse
4. THREAD DIRECTION : Right Hand
5. THREAD STYLE : Fully Threaded
6. TEMP. RANGE : - 58°F to 302°F
7. STANDARD : ASME B18.3
8. ROCKWELL HARDNESS : C37 to C44
9. MIN.TENSILE STRENGTH : 135,000 psi

COMPONENT

Socket Head Cap Screw

UNIT

INCH

SHEET

1 of 1

GRAINGER

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE

3.52

26LC71

SHCS, Flat, Steel, 1/4-20x3/4, PK100