

1.40
Max. Sec.

Ø 10.80
Free O.D.

3.20
Lug Ht.

Ø 1.20
Hole Dia.

1.00
Thickness

NOTES:

ITEM : Retaining Ring
 TYPE : Internal
 MATERIAL : Spring Steel
 FINISH : Plain
 FOR BORE DIA : 10mm
 PACKAGE QUANTITY : 100

GRAINGER
 //

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE

6.40

COMPONENT

Retaining Ring

38DN44

Retaining Ring for Bores,10mm,PK100

UNIT

MM

SHEET

1 of 1