

5.10  
Max. Sec.

Ø 60.20  
Free O.D.

Ø 2.50  
Hole Dia.

6.80  
Lug Ht.

2.00  
Thickness

NOTES:

ITEM : Retaining Ring  
TYPE : Internal  
MATERIAL : Spring Steel  
FINISH : Plain  
FOR BORE DIA : 56mm  
PACKAGE QUANTITY : 10

**GRAINGER**  
////////

100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE

1.10

COMPONENT

Retaining Ring

**38DN88**

Retaining Ring for Bores,56mm,PK10

UNIT

MM

SHEET

1 of 1