

0.040
Max. Sec.

Ø 0.415
Free O.D.

0.028
Min. Sec.

0.082
Lug Ht.

Ø 0.041
Hole Dia.

0.025
Thickness

NOTES:

ITEM : Retaining Ring
TYPE : Internal
MATERIAL : Carbon Steel
FINISH : Plain
FOR BORE DIA : 3/8"
PACKAGE QUANTITY : 50

GRAINGER
////////

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE

6.50

COMPONENT

Retaining Ring

41MG99

Retaining Ring, Inter, 3/8in Bore, PK50

UNIT

INCH

SHEET

1 of 1