



NOTES:

1. ITEM: Hex Locknut
2. TEMP. RANGE: -20° to 150°F
3. FITTING CONNECTION TYPE: FNPT
4. PIPE SIZE - PIPE FITTING: 1-1/2"
5. FITTING SCHEDULE/CLASS: Class 150
6. MAX. PRESSURE: 300 psi @ 150°F WOG
7. PIPE FITTING MATERIAL: Galvanized Malleable Iron
8. STANDARDS: ANSI B 16.39, Material Specification ASTM A-197,
Dimensions Conform to Federal Specifications WW-P-521

COMPONENT		Galvanized Pipe Fitting	
5P983		UNIT	
		INCH	
		SHEET	
		1 of 1	
Hex Locknut, 1 1/2 In, Galvanized			

GRAINGER

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.33