



LADDER CROSS-REFERENCE CATALOG

Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

FIBERGLASS STEPLADDERS

ANSI IAA Load Capacity: 375 lbs		7400 SERIES STEPLADDER Patented EDGE® bracing provides enhanced bottom bracing strength and increased protection against damage. Aluminum external rail shields provide additional reinforcement to the bottom. Full set of large heavy duty aluminum knee braces on all front steps and all rear horizontals. Heavy-duty aluminum Tool-Tra-Top® securely holds drills and other tools. Internal spreader bars.	
---	--	--	--

4XN71	4 FT	Werner 7404	Ladder Height 4', Approx. Shipping Weight 16.5 lbs., Base Spread 30-1/2", Bottom Width 21-1/2"
3AZX4	5 FT	Werner 7405	Ladder Height 5', Approx. Shipping Weight 20.0 lbs., Base Spread 36-3/4", Bottom Width 23-1/4"
4XN72	6 FT	Werner 7406	Ladder Height 6', Approx. Shipping Weight 23.5 lbs., Base Spread 42-7/8", Bottom Width 25"
3AZX5	7 FT	Werner 7407	Ladder Height 7', Approx. Shipping Weight 28.0 lbs., Base Spread 49", Bottom Width 26-3/4"
4XN73	8 FT	Werner 7408	Ladder Height 8', Approx. Shipping Weight 32.0 lbs., Base Spread 55-1/4", Bottom Width 28-1/2"
4XN74	10 FT	Werner 7410	Ladder Height 10', Approx. Shipping Weight 40.5 lbs., Base Spread 67-1/2", Bottom Width 32"
4XN75	12 FT	Werner 7412	Ladder Height 12', Approx. Shipping Weight 49.5 lbs., Base Spread 79-7/8", Bottom Width 35-1/2"



ANSI IAA Load Capacity: 375 lbs		7300 SERIES STEPLADDER Patented EDGE® bracing provides enhanced bottom bracing strength and increased protection against damage. Molded non-conductive external rail shields helps protect bottom from damage. Large heavy duty aluminum knee braces on all front steps and all rear horizontals. Heavy-duty aluminum Tool-Tra-Top® securely holds drills and other tools. Internal spreader bars.	
---	--	---	--

6JJ81	4 FT	Werner 7304	Ladder Height 4', Approx. Shipping Weight 16.0 lbs., Base Spread 29-3/4", Bottom Width 21-1/2"
3AZX3	5 FT	Werner 7305	Ladder Height 5', Approx. Shipping Weight 19.5 lbs., Base Spread 35-7/8", Bottom Width 23-1/4"
6JJ82	6 FT	Werner 7306	Ladder Height 6', Approx. Shipping Weight 22.5 lbs., Base Spread 42", Bottom Width 25"
6JJ83	8 FT	Werner 7308	Ladder Height 8', Approx. Shipping Weight 31.0 lbs., Base Spread 54-3/4", Bottom Width 28-1/2"
6JJ84	10 FT	Werner 7310	Ladder Height 10', Approx. Shipping Weight 40.5 lbs., Base Spread 66-5/8", Bottom Width 32"
6JJ85	12 FT	Werner 7312	Ladder Height 12', Approx. Shipping Weight 49.5 lbs., Base Spread 79", Bottom Width 35-1/2"



ANSI IAA Load Capacity: 375 lbs		6300 SERIES STEPLADDER Patented EDGE360™ feet provide protection from every angle with integrated rail shield, EDGE Bracing and Over-Sized feet and foot pads. Feature rich LOCKTOP™ with slots to accommodate Lock-In accessories such as the ToolLasso and JobBucket. Double riveted, slip-resistant Traction-Tred® steps. All steps and are knee-braced. Full set of rear horizontals. Internal Spreader Bars.	
---	--	--	--

29JV18	4 FT	Werner 6304	Ladder Height 4', Approx. Shipping Weight 16.0 lbs., Base Spread 29", Bottom Width 19 7/8"
29JV20	5 FT	Werner 6305	Ladder Height 5', Approx. Shipping Weight 19.0 lbs., Base Spread 35-1/8", Bottom Width 21 5/8"
29JV21	6 FT	Werner 6306	Ladder Height 6', Approx. Shipping Weight 22.0 lbs., Base Spread 41-1/4", Bottom Width 23 3/8"
29JV23	8 FT	Werner 6308	Ladder Height 8', Approx. Shipping Weight 31.0 lbs., Base Spread 53-5/8", Bottom Width 27 7/8"
29JV25	10 FT	Werner 6310	Ladder Height 10', Approx. Shipping Weight 39.0 lbs., Base Spread 65-7/8", Bottom Width 30 3/8"
29JV27	12 FT	Werner 6312	Ladder Height 12', Approx. Shipping Weight 48.0 lbs., Base Spread 78-1/4", Bottom Width 33 7/8"



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

FIBERGLASS STEPLADDERS *continued*

6200 SERIES STEPLADDER
ANSI IA
Load Capacity: 300 lbs
 Patented EDGE360™ feet provide protection from every angle with integrated rail shield, EDGE Bracing and Over-Sized feet and foot pads. Feature rich LOCKTOP™ with slots to accommodate Lock-In accessories such as the ToolLasso and JobBucket. Double riveted, slip-resistant Traction-Tred® steps. All steps and are knee-braced. Full set of rear horizontals. Internal Spreader Bars.

41D245	3 FT	Werner 6203	Ladder Height 3', Approx. Shipping Weight 13.0#, Base Spread 23-1/8", Bottom Width 18-1/8"
3W421	4 FT	Werner 6204	Ladder Height 4', Approx. Shipping Weight 16.0 lbs., Base Spread 29", Bottom Width 19-7/8"
3AZX1	5 FT	Werner 6205	Ladder Height 5', Approx. Shipping Weight 19.0 lbs., Base Spread 35-1/8" , Bottom Width 21-5/8"
3W141	6 FT	Werner 6206	Ladder Height 6', Approx. Shipping Weight 22.0 lbs., Base Spread 41-1/4", Bottom Width 23-3/8"
3AZX2	7 FT	Werner 6207	Ladder Height 7', Approx. Shipping Weight 26.0 lbs., Base Spread 47-1/2", Bottom Width 25-1/8"
3W142	8 FT	Werner 6208	Ladder Height 8', Approx. Shipping Weight 30.0 lbs., Base Spread 53-5/8", Bottom Width 26-7/8"
3W183	10 FT	Werner 6210	Ladder Height 10', Approx. Shipping Weight 39.0 lbs., Base Spread 65-7/8", Bottom Width 30-3/8"
3W422	12 FT	Werner 6212	Ladder Height 12', Approx. Shipping Weight 48.0 lbs., Base Spread 78-1/4", Bottom Width 33-7/8"



6100 SERIES STEPLADDER
ANSI IA
Load Capacity: 300 lbs
 Patented, molded, versatile HolsterTop® securely holds drills and other tools. Top is designed with sockets in back to accommodate Lock-In accessories such as the ToolLasso and JobBucket. Double riveted, slip-resistant Traction-Tred® steps. Full set of rear horizontals. Oversized, molded PROGUARD BOOTS™ provide firm slip-resistant footing and protect fiberglass rail. Internal spreader bars.

29JV19	4 FT	Werner 6104	Ladder Height 4', Approx. Shipping Weight 15.0 lbs., Base Spread 28-7/8", Bottom Width 19"
29JV22	6 FT	Werner 6106	Ladder Height 6', Approx. Shipping Weight 21.0 lbs., Base Spread 41-1/8", Bottom Width 22"
29JV24	8 FT	Werner 6108	Ladder Height 8', Approx. Shipping Weight 30.0 lbs., Base Spread 53-1/2", Bottom Width 25"
29JV26	10 FT	Werner 6110	Ladder Height 10', Approx. Shipping Weight 35.5 lbs., Base Spread 65-3/4", Bottom Width 28"
29JV28	12 FT	Werner 6112	Ladder Height 12', Approx. Shipping Weight 44.0 lbs., Base Spread 78-1/8", Bottom Width 31"



6000 SERIES STEPLADDER
ANSI I
Load Capacity: 250 lbs
 Patented EDGE® bracing provides enhanced bottom bracing strength and increased protection against damage. Patented, molded, versatile HolsterTop® securely holds drills and other tools. Top is designed with sockets in back to accommodate Lock-In Accessories such as the ToolLasso® and JobBucket. External spreader bars.

4W077	4 FT	Werner 6004	Ladder Height 4', Approx. Shipping Weight 13.0 lbs., Base Spread 28-7/8", Bottom Width 19"
6AZW9	5 FT	Werner 6005	Ladder Height 5', Approx. Shipping Weight 16.0 lbs., Base Spread 35", Bottom Width 20-1/2"
4W078	6 FT	Werner 6006	Ladder Height 6', Approx. Shipping Weight 18.0 lbs., Base Spread 41-1/8", Bottom Width 22"
4W079	8 FT	Werner 6008	Ladder Height 8', Approx. Shipping Weight 25.5 lbs., Base Spread 53-1/2", Bottom Width 25"



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

FIBERGLASS TWIN STEPLADDERS

ANSI IAA / IA
Load Capacity: 375 / 300 lbs (per side)

T7400 SERIES TWIN STEPLADDER
Twin Stepladders are great for two-person jobs. Patented EDGE® bracing provides enhanced bottom bracing strength and increased protection against damage. Aluminum external rail shields provide additional reinforcement to the bottom. Large heavy duty aluminum knee braces on all front and back steps. Heavy-duty aluminum Tool-Tra-Top®. Internal Spreader Bars.

4XP48	4 FT 375 lbs	Werner T7404	Ladder Height 4', Approx. Shipping Weight 21.5 lbs., Base Spread 36-1/8", Bottom Width 21-1/2"
41D242	5 FT 375 lbs	Werner T7405	Ladder Height 5', Approx. Shipping Weight 29.0#, Base Spread 43-1/8", Bottom Width 23-1/2"
4XP49	6 FT 375 lbs	Werner T7406	Ladder Height 6', Approx. Shipping Weight 30.0 lbs., Base Spread 50-1/8", Bottom Width 25"
4XP50	8 FT 375 lbs	Werner T7408	Ladder Height 8', Approx. Shipping Weight 40.5 lbs., Base Spread 64-1/8", Bottom Width 28-1/2"
4XP51	10 FT 375 lbs	Werner T7410	Ladder Height 10', Approx. Shipping Weight 51.5 lbs., Base Spread 78-1/4", Bottom Width 32"
4XP52	12 FT 375 lbs	Werner T7412	Ladder Height 12', Approx. Shipping Weight 63.5 lbs., Base Spread 92-1/4", Bottom Width 35-1/2"
4XP53	14 FT 300 lbs	Werner T7414	Ladder Height 14', Approx. Shipping Weight 86.0 lbs., Base Spread 106-1/4", Bottom Width 39"
4XP54	16 FT 300 lbs	Werner T7416	Ladder Height 16', Approx. Shipping Weight 103.5 lbs., Base Spread 120-1/4", Bottom Width 42-1/8"
4XP55	20 FT 300 lbs	Werner T7420	Ladder Height 20', Approx. Shipping Weight 149.0 lbs., Base Spread 150-1/8", Bottom Width 49-1/2"



ANSI IA
Load Capacity: 300 lbs (per side)

T6200 SERIES STEPLADDER
Twin Stepladders are great for two-person jobs. Patented moded versatile HolsterTop® securely holds drills and other tools. Slip-resistant Traction-Tred® steps are double riveted. Patented EDGE360™ feet provide protection from every angle with integrated rail shield, EDGE Bracing and over-sized feet and foot pads.

6YG79	4 FT	Werner T6204	Ladder Height 4', Approx. Shipping Weight 19.0 lbs., Base Spread 36-1/8", Bottom Width 19-7/8"
3AZX6	5 FT	Werner T6205	Ladder Height 5', Approx. Shipping Weight 23.0 lbs., Base Spread 43-1/8", Bottom Width 21-5/8"
6YG80	6 FT	Werner T6206	Ladder Height 6', Approx. Shipping Weight 27.0 lbs., Base Spread 50-1/8", Bottom Width 23-3/8"
6YG81	8 FT	Werner T6208	Ladder Height 8', Approx. Shipping Weight 37.0 lbs., Base Spread 64-1/8", Bottom Width 26-7/8"
3AZX7	10 FT	Werner T6210	Ladder Height 10', Approx. Shipping Weight 54.5 lbs., Base Spread 78-1/8", Bottom Width 30-3/8"
3AZX8	12 FT	Werner T6212	Ladder Height 12', Approx. Shipping Weight 68.5 lbs., Base Spread 92-1/8", Bottom Width 33-7/8"



ANSI IAA
Load Capacity: 375 lbs

PD7300 SERIES PODIUM LADDER
Ideal for working at fixed heights. Extra large platform for long standing comfort and allows you to work safely in any direction. Waist high guard rail wraps around work zone and securely holds tools. Slip-resistant steps are knee-braced and double riveted. The EDGE360® bracing system gives protection from every angle and oversized foot pads.

36FX50	6 FT	Werner PD7303	Ladder Height 6', Platform Height is 3'. Approx. Ship Weight 22.5 lbs., Base Spread 36", Bottom Width 26 "
36FX51	7 FT	Werner PD7304	Ladder Height 7', Platform Height is 4'. Approx. Ship Weight 28.0 lbs., Base Spread 42", Bottom Width 27 "
36FX52	9 FT	Werner PD7306	Ladder Height 9', Platform Height is 6'. Approx. Ship Weight 34 lbs., Base Spread 55", Bottom Width 31"
36FX53	11 FT	Werner PD7308	Ladder Height 11', Platform Height is 8'. Approx. Ship Weight 46 lbs., Base Spread 69", Bottom Width 35 "



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

FIBERGLASS PODIUM LADDERS

ANSI IA Load Capacity: 300 lbs		PD6200 SERIES PODIUM LADDER Ideal for working at fixed heights. Extra large platform for long standing comfort and allows you to work safely in any direction. Waist high guard rail wraps around work zone and securely holds tools. Slip-resistant steps are knee-braced and double riveted. The EDGE360® bracing system gives protection from every angle. Oversized foot pads.	
20KJ26	6 FT	Werner PD6203	Ladder Height 6', Platform Height is 3'. Approx. Ship Weight 22.5#, Base Spread 36", Bottom Width 26 "
20KJ27	7 FT	Werner PD6204	Ladder Height 7', Platform Height is 4'. Approx. Ship Weight 28.0#, Base Spread 42", Bottom Width 27 "
20KJ28	9 FT	Werner PD6206	Ladder Height 9', Platform Height is 6'. Approx. Ship Weight 34#, Base Spread 55", Bottom Width 31"
20KJ29	11 FT	Werner PD6208	Ladder Height 11', Platform Height is 8'. Approx. Ship Weight 46#, Base Spread 69", Bottom Width 35 "
20KJ30	13 FT	Werner PD6210	Ladder Height 13', Platform Height is 10'. Approx. Ship Weight 57#, Base Spread 79", Bottom Width 38"



FIBERGLASS PLATFORM LADDERS

ANSI IAA / IA Load Capacity: 375 / 300 lbs		P7400 SERIES PLATFORM STEPLADDER Safety guard rail encourages proper ladder use. Large platform provides secure and comfortable work area. Slip-resistant Traction-Tred® extra wide steps are knee-braced and double riveted. The EDGE® bracing system helps to decrease damage to rail. Aluminum external rail shields provide additional reinforcement to the bottom.	
6W679	6 FT 375 lbs	Werner P7404	Ladder Height 6', Platform Height 4'. Approx. Shipping Weight 26.0 lbs., Base Spread 42", Bottom Width 27"
3W186	8 FT 375 lbs	Werner P7406	Ladder Height 8', Platform Height 6'. Approx. Shipping Weight 34.0 lbs., Base Spread 54-3/8", Bottom Width 30-1/2"
6W680	10 FT 375 lbs	Werner P7408	Ladder Height 10', Platform Height 8'. Approx. Shipping Weight 44.5 lbs., Base Spread 66-5/8", Bottom Width 34"
4XP29	12 FT 300 lbs	Werner P7410	Ladder Height 12', Platform Height 10'. Approx. Shipping Weight 54.5 lbs., Base Spread 79", Bottom Width 37-1/2 "



ANSI IA Load Capacity: 300 lbs		P6200 SERIES STEPLADDER Safety guard rail encourages proper ladder use. Large platform provides secure and comfortable work area. Slip-resistant Traction-Tred® steps are double riveted. Patented EDGE360™ feet provide protection from every angle with integrated rail shield, EDGE Bracing and over-sized feet and foot pads.	
4EB96	6 FT	Werner P6204	Ladder Height 6', Platform Height 4', Approx. Shipping Weight 24.0 lbs., Base Spread 42" , Bottom Width 26-7/8 "
4EB97	8 FT	Werner P6206	Ladder Height 8', Platform Height 6', Approx. Shipping Weight 32.0 lbs., Base Spread 54-3/4", Bottom Width 30-3/8"
4EB98	10 FT	Werner P6208	Ladder Height 10', Platform Height 8', Approx. Shipping Weight 44.5 lbs., Base Spread 66-5/8", Bottom Width 33-7/8"
3AZY5	12 FT	Werner P6210	Ladder Height 12', Platform Height 10', Approx. Shipping Weight 55.0 lbs., Base Spread 79", Bottom Width 37-3/8"



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

FIBERGLASS STOCKR'S® LADDERS

ANSI IA Load Capacity: 300 lbs (per side)		PT7400-4C SERIES STOCKR'S LADDER® Safety guard rail. Large platform. Slip-resistant Traction-Tred® steps on front and rear sections. Soft rubber wheels are easy on vinyl floors and designed to roll over thresholds. 4 spring-loaded casters allow easy 360° mobility.	
---	--	---	--

3AZY6	6 FT	Werner PT7404-4C	Ladder Height 6', Platform Height 4', Approx. Shipping Weight 37.0 lbs., Base Spread 50", Bottom Width 25-1/4"
4XP39	8 FT	Werner PT7406-4C	Ladder Height 8', Platform Height 6', Approx. Shipping Weight 53.0 lbs., Base Spread 64", Bottom Width 28-3/4"
4XP40	10 FT	Werner PT7408-4C	Ladder Height 10', Platform Height 8', Approx. Shipping Weight 60.5 lbs., Base Spread 78-1/4", Bottom Width 32-1/4"
4XP41	12 FT	Werner PT7410-4C	Ladder Height 12', Platform Height 10', Approx. Shipping Weight 72.5 lbs., Base Spread 92-1/4", Bottom Width 35-3/4"



ANSI I Load Capacity: 250 lbs (per side)		PT7400-4C SERIES STOCKR'S LADDER® Safety guard rail. Large platform. Slip-resistant Traction-Tred® steps on front and rear sections. Soft rubber wheels are easy on vinyl floors and designed to roll over thresholds. 4 spring-loaded casters allow easy 360° mobility.	
--	--	---	--

4XP36	6 FT.	Werner PT6004-4C	Ladder Height 6', Platform Height 4', Approx. Shipping Weight 35.0 lbs., Base Spread 51", Bottom Width is 23"
4XP37	8 FT.	Werner PT6006-4C	Ladder Height 8', Platform Height 6', Approx. Shipping Weight 47.0 lbs., Base Spread 65-1/2", Bottom Width 26"
4XP38	10 FT.	Werner PT6008-4C	Ladder Height 10', Platform Height 8', Approx. Shipping Weight 64.5 lbs., Base Spread 80", Bottom Width 29"



FIBERGLASS TRIPOD LADDER

ANSI IA Load Capacity: 300 lbs		FTP6200 SERIES TRIPOD STEPLADDER Tripod ladders make it possible to work in tight areas, around corners, and through studs. 3-legged design stays stable on uneven surfaces. Molded, versatile top securely holds drills and many other tools.	
--	--	---	--

4ZY19	4 FT	Werner FTP6204	Ladder Height 4', Approx. Shipping Weight 17.0 lbs., Base Spread 30-1/2", Bottom Width 31"
4EB99	6 FT	Werner FTP6206	Ladder Height 6', Approx. Shipping Weight 23.0 lbs., Base Spread 43-3/4", Bottom Width 36"
4ZY20	8 FT	Werner FTP6208	Ladder Height 8', Approx. Shipping Weight 31.0 lbs., Base Spread 57", Bottom Width 40"
41D249	10 FT	Werner FTP6210	Ladder Height 10', Approx. Ship Wt. 42.0#, Base Spread 71", Bottom Width 51"
41D250	12 FT	Werner FTP6212	Ladder Height 12', Approx. Ship Wt. 51.0#, Base Spread 77-3/4", Bottom Width 54"



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

ELECTRICIAN'S JOBSTATION™

ANSI IAA Load Capacity: 375 lbs			OBEL00 SERIES ELECTRICIAN'S JOBSTATION™ Specifically designed for the electrical contractor with integrated retractable conduit holder, wire spool holders and multi-use hook. Custom designed HolsterTop® is equipped with groove to hold pipes up to 1" diameter and includes measuring scale and tool slots. Top is designed with sockets in back to accommodate Lock-In Accessories such as the ToolLasso® and JobBucket.
1FCF1	4 FT	Werner OBEL04	Ladder Height 4', Approx. Shipping Weight 16.0 lbs., Base Spread 29", Base Width 19-7/8" Note: Conduit holder not available on 4' model
1FCF2	6 FT	Werner OBEL06	Ladder Height 6', Approx. Shipping Weight 24.0 lbs., Base Spread 41-1/4", Bottom Width 23-3/8"
1FCF3	8 FT	Werner OBEL08	Ladder Height 8', Approx. Shipping Weight 32.0 lbs., Base Spread 53-5/8", Bottom Width 26-7/8"
1FCF4	10 FT	Werner OBEL10	Ladder Height 10', Approx. Shipping Weight 41.0 lbs., Base Spread 65-7/8", Bottom Width 30-3/8"
1FCF5	12 FT	Werner OBEL12	Ladder Height 12', Approx. Shipping Weight 51.5 lbs., Base Spread 78-1/4", Bottom Width 33-7/8"



FIBERGLASS EXTENSION/TRESTLE LADDER

ANSI IA Load Capacity: 300 lbs (per side)			E7400 SERIES EXTENSION/TRESTLE LADDER Twin stepladders with extendable trestle section. Patented EDGE® bracing provides enhanced bottom bracing strength and increased protection against damage. Aluminum external rail shields provide additional reinforcement to the bottom.
4XP05	8 FT	Werner E7408	Stepladder Height 8', Extended Ladder Height 12', Base Section Width 32-3/4", Spread 67-3/4"
4XP06	10 ft.	Werner E7410	Stepladder Height 10', Extended Ladder Height 15', Base Section Width 36-1/4", Spread 81-7/8"
4XP07	12 FT	Werner E7412	Stepladder Height 12', Extended Ladder Height 19', Base Section Width 39-3/4", Spread 95-7/8"
4XP08	14 FT	Werner E7414	Stepladder Height 14', Extended Ladder Height 22', Base Section Width 43-1/4", Spread 109-3/4"
4XP09	16 FT	Werner E7416	Stepladder Height 16', Extended Ladder Height 26', Base Section Width 46-3/4", Spread 123-3/4"



FIBERGLASS COMBINATION LADDERS

ANSI IAA Load Capacity: 375 lbs			7800 SERIES FIBERGLASS COMBINATION STEP/EXTENSION LADDERS Fiberglass combination ladders provide dual functionality in one ladder. Easily converts from a stepladder to extension ladder and back. ALFLO® rung joint connections.
4XN76	6 FT	Werner 7806	Stepladder Height 6', Extended ladder working length 9-1/2'. Base Width 23-1/4" at flared base, Stepladder spread to outside of shoes 46-1/2", Approx. Shipping Weight 33.5 lbs.
6W679	7 FT	Werner 7807	Stepladder Height 7', Extended ladder working length 11-1/2'. Base Width 24-1/4" at flared base, Stepladder spread to outside of shoes 53-1/2", Approx. Shipping Weight 37.0 lbs.
4XN77	8 FT	Werner 7808	Stepladder Height 8', Extended ladder working length 13-1/2'. Base Width 25-1/4" at flared base, Stepladder spread to outside of shoes 60-1/2", Approx. Shipping Weight 40.5 lbs.



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

ALUMINUM STEPLADDERS

ANSI IAA / IA Load Capacity: 375 / 300 lbs		400 SERIES STEPLADDER Aluminum stepladder features heavy gauge aluminum Tool-Tra-Top®. All steps are knee braced. Slip-resistant Traction-Tred® steps. Full set of rear horizontals. Slip-resistant foot pads.	
---	--	--	--

4XN58	4 FT 375 lbs	Werner 404	Ladder Height 4', Approx. Shipping Weight 16.0 lbs., Base Spread 30-1/8", Bottom Width 21-1/4"
4XN59	6 FT 375 lbs	Werner 406	Ladder Height 6', Approx. Shipping Weight 24.0 lbs., Base Spread 42-7/16", Bottom Width 24-3/4"
4XN60	8 FT 375 lbs	Werner 408	Ladder Height 8', Approx. Shipping Weight 33.5 lbs., Base Spread 54-3/4", Bottom Width 28-1/4"
4XN61	10 FT 375 lbs	Werner 410	Ladder Height 10', Approx. Shipping Weight 43.5 lbs., Base Spread 67", Bottom Width 31-1/4"
4XN63	12 FT 375 lbs	Werner 412	Ladder Height 12', Approx. Shipping Weight 54.5 lbs., Base Spread 79-3/8", Bottom Width 35-1/4"
4XN64	14 FT 300 lbs	Werner 414	Ladder Height 14', Approx. Shipping Weight 65.0 lbs., Base Spread 91-11/16", Bottom Width 38-5/8"
4XN67	16 FT 300 lbs	Werner 416	Ladder Height 16', Approx. Shipping Weight 77.5 lbs., Base Spread 104", Bottom Width 42-1/8"



ANSI IA Load Capacity: 300 lbs		370 SERIES STEPLADDER Aluminum stepladder features Tool-Tra-Top®. Sturdy Spill-Proof® pail shelf. Double riveted slip-resistant Traction-Tred® steps. Full set of rear horizontals. Unique "H" spreader with hand grip on 4', 5' and 6' for easy one-handed carry and close.	
-----------------------------------	--	--	--

2EJG8	3 FT	Werner 373	Ladder Height 3', Approx. Shipping Weight 9.0 lbs., Base Spread 23-3/8", Bottom Width 17-3/4"
4W074	4 FT	Werner 374	Ladder Height 4', Approx. Shipping Weight 11.0 lbs., Base Spread 29-1/2", Bottom Width 19-1/2"
3AZX9	5 FT	Werner 375	Ladder Height 5', Approx. Shipping Weight 13.5 lbs., Base Spread 35-3/4", Bottom Width 21-1/4"
3W423	6 FT	Werner 376	Ladder Height 6', Approx. Shipping Weight 15.5 lbs., Base Spread 41-7/8", Bottom Width 23"
3W424	8 FT	Werner 378	Ladder Height 8', Approx. Shipping Weight 22.5 lbs., Base Spread 54-1/4", Bottom Width 26-1/2"
4W172	10 FT	Werner 310	Ladder Height 10', Approx. Shipping Weight 31.0 lbs., Base Spread 66-1/2", Bottom Width 30"



ANSI IAA Load Capacity: 375 lbs		360 SERIES STEPLADDER Aluminum stepladder features Tool-Tra-Top® with convenient tray for tools, paint can and slots for paint roller tray and paint can hanger on back. Automatic Spill-Proof® pail shelf that opens and closes with ladder and has slots to hold tools, rag bar and paint can. Slip-resistant molded feet. External spreader bars.	
------------------------------------	--	--	--

41D304	4 FT	Werner 364	Ladder Height 4' Approx. Ship Weight 10.5 lbs., Base Spread 29 1/4", Bottom Width 18 1/2"
41D305	5 FT	Werner 365	Ladder Height 5' Approx. Ship Weight 12.5 lbs., Base Spread 35 1/2", Bottom Width 20"
41D306	6 FT	Werner 366	Ladder Height 6' Approx. Ship Weight 14.5 lbs., Base Spread 41 5/8", Bottom Width 21 1/2 "
4GNK8	8 FT	Werner 368	Ladder Height 8' Approx. Ship Weight 21.5 lbs., Base Spread 54", Bottom Width 24 1/2 "



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

ALUMINUM TWIN STEPLADDERS

ANSI IAA Load Capacity: 300 lbs (per side)		T370 SERIES TWIN STEPLADDER Twin Stepladders are great for two-person jobs. Double riveted slip-resistant Traction-Tred® steps. Full set of rear horizontals. Internal spreader bars.	
3AZY1	4 FT	Werner T374	Ladder Height 4', Approx. Shipping Weight 14.5 lbs., Base Spread 36", Bottom Width 21-1/4"
3AZY2	6 FT	Werner T376	Ladder Height 6', Approx. Shipping Weight 21.5 lbs., Base Spread 50", Bottom Width 24-3/4"
3AZY3	8 FT	Werner T378	Ladder Height 8', Approx. Shipping Weight 31.0 lbs., Base Spread 64", Bottom Width 28-1/4"
3AZY4	10 FT	Werner T310	Ladder Height 10', Approx. Shipping Weight 43.0 lbs., Base Spread 78", Bottom Width 31-3/4"



ALUMINUM PLATFORM LADDERS

ANSI IAA Load Capacity: 375 lbs		P400 SERIES PLATFORM STEPLADDER Large platform provides secure and comfortable work area with safety guard rail. Features 225 square inches of platform standing area. Heavy duty knee bracing on all front steps. Shoulder bolt with locknut on top hinge.	
6W686	6 FT	Werner P404	Ladder Height 6', Platform Height 4', Approx. Shipping Weight 25.0 lbs., Base Spread 42-1/16", Bottom Width 24-3/4"
6W687	8 FT	Werner P406	Ladder Height 8', Platform Height 6', Approx. Shipping Weight 33.5 lbs., Base Spread 54-3/4", Bottom Width 28-1/4"
6W688	10 FT	Werner P408	Ladder Height 10', Platform Height 8', Approx. Shipping Weight 45.5 lbs., Base Spread 79-1/2", Bottom Width 31-3/4"



ALUMINUM STOCKR'S® LADDERS

ANSI IAA Load Capacity: 300 lbs (per side)		PT370 SERIES STOCKR'S LADDER® Large platform allows comfortable, secure work platform with safety guard rail. Pinch-Proof™ platform is designed for easy opening and folding. Easy to handle and folds to a 10" width for storage	
3AZY7	6 FT	Werner PT374	Ladder Height 6', Platform Height 4', Approx. Shipping Weight 27.0 lbs., Base Spread 50-1/2", Bottom Width 24-3/4"
3AZY8	8 FT	Werner PT376	Ladder Height 8', Platform Height 6', Approx. Shipping Weight 36.0 lbs., Base Spread 65-1/4", Bottom Width 28-1/4"
3AZY9	10 FT	Werner PT378	Ladder Height 10', Platform Height 8', Approx. Shipping Weight 46.5 lbs., Base Spread 81-1/2", Bottom Width 34-1/4"



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

ALUMINUM UTILITY LADDERS

ANSI III Load Capacity: 200 lbs		MODEL 244 ALUMINUM UTILITY LADDER Lightweight - easy to open and close. Features comfortable tubular rails, slip-resistant steps, and mar-resistant feet. Compact for convenient storage - folds to 3"	
------------------------------------	--	--	--

4XN47	3.5 FT	Werner 244	Rail Length is 3-1/2'; Second step is at 23"
-------	--------	------------	--



ALUMINUM PLATFORM UTILITY

ANSI III Load Capacity: 200 lbs		260 SERIES PLATFORM UTILITY LADDER Spill-Proof [®] pail holder with rag rail. Large comfortable slip-resistant platform. Mar-resistant feet. Compact for convenient storage - folds to 3-1/2"	
------------------------------------	--	--	--

4XN54	4.5 FT	Werner 264	Ladder Height 4.5', Platform Height 22.5, Approx. Shipping Weight 11.5 lbs. Base spread 25-1/2", Bottom Width 20"
-------	--------	------------	---



4XN55	5.5 FT	Werner 265	Ladder Height 5.5', Platform Height 33.5", Approx. Shipping Weight 15.0 lbs., Base Spread 33-1/4", Bottom Width 21-1/2"
-------	--------	------------	---

ALUMINUM TELESCOPING MULTIPURPOSE LADDERS

ANSI IA Load Capacity: 300 lbs		MT SERIES TELESCOPING MULTILADDER Easily converts into 4 positions - Twin Stepladder, Stairway Ladder, Extension Ladder, 2-Scaffold Bases. Smooth curved rails for comfortable climbing. Double riveted steps for long lasting durability. Extra wide flared bottom for firm support. Slip-resistant feet.	
-----------------------------------	--	--	--

2NKW6	13 FT	Werner MT-13	Stepladder Height = 3' to 5' Extension Ladder Height = 7' to 11' Stairway Ladder Height = 3' to 5' Scaffold Position Length = 1' to 2' Weight = 31.6 lbs.
-------	-------	--------------	---

2NKW7	17 FT	Werner MT-17	Stepladder Height = 4' to 7' Extension Ladder Height = 9' to 15' Stairway Ladder Height = 4' to 7' Scaffold Position Length = 1' to 3' Weight = 39.6 lbs.
-------	-------	--------------	---

2NKW8	22 FT	Werner MT-22	Stepladder Height = 5' to 9' Extension Ladder Height = 11' to 19' Stairway Ladder Height = 5' to 9' Scaffold Position Length = 1' to 4' Weight = 47.0 lbs.
-------	-------	--------------	--

2NKW9	26 FT	Werner MT-26	Stepladder Height = 6' to 11' Extension Ladder Height = 13' to 23' Stairway Ladder Height = 6' to 11' Scaffold Position Length = 1' to 5' Weight = 62.6 lbs.
-------	-------	--------------	--




Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

FIBERGLASS EXTENSION LADDERS

ANSI IAA / IA Load Capacity: (375 / 300 lbs as noted)		D7100-2 SERIES EXTENSION LADDER ALFLO® rung joints for Twist-Proof® performance. Rung plate connection for easy rung replacement. Slip-resistant Traction-Tred® D-rungs. Combination shoes with slip-resistant rubber pads for hard surfaces or swivel the shoe to use the spur plates for penetrable surfaces. Note: 16' No. 4XN97 is not equipped with rope and pulley.	
--	--	---	--

4XN97	16 FT 375 lbs	Werner D7116-2	Ladder Height 16', Maximum Working Length 13', Approx. Shipping Weight 41.0 lbs.
4XN98	20 FT 375 lbs	Werner D7120-2	Ladder Height 20', Maximum Working Length 17', Approx. Shipping Weight 50.0 lbs.
4XN99	24 FT 375 lbs	Werner D7124-2	Ladder Height 24', Maximum Working Length 21', Approx. Shipping Weight 58.5 lbs.
4XP01	28 FT 375 lbs	Werner D7128-2	Ladder Height 28', Maximum Working Length 25', Approx. Shipping Weight 67.0 lbs.
4XP02	32 FT 375 lbs	Werner D7132-2	Ladder Height 32', Maximum Working Length 29', Approx. Shipping Weight 82.5 lbs.
3W621	40 FT 300 lbs	Werner D7140-2	Ladder Height 40', Maximum Working Length 35', Approx. Shipping Weight 126.5 lbs.



Rung-plate connection

ANSI IA Load Capacity: 300 lbs		D6200-2 SERIES EXTENSION LADDER ALFLO® rung joints for Twist-Proof® performance. Direct rung to rail connections. Slip-resistant Traction-Tred® rungs. Combination shoes with slip-resistant rubber pads for hard surfaces or swivel the shoe to use the spur plates for penetrable surfaces. Note: 16' Item 3W620 is not equipped with rope and pulley.	
-----------------------------------	--	--	--

3W620	16 FT	Werner D6216-2	Ladder Height 16', Maximum Working Length 13', Approx. Shipping Weight 36.5 lbs.
3W184	20 FT	Werner D6220-2	Ladder Height 20', Maximum Working Length 17', Approx. Shipping Weight 44.5 lbs.
3W139	24 FT	Werner D6224-2	Ladder Height 24', Maximum Working Length 21', Approx. Shipping Weight 52.0 lbs.
3W140	28 FT	Werner D6228-2	Ladder Height 28', Maximum Working Length 25', Approx. Shipping Weight 59.5 lbs.
3W185	32 FT	Werner D6232-2	Ladder Height 32', Maximum Working Length 29', Approx. Shipping Weight 71.5 lbs.
4XP10	40 FT	Werner D6240-2	Ladder Height 40', Maximum Working Length 35', Approx. Shipping Weight 88.5 lbs.



ALFLO® Rung-to-Rail connect-on

ALUMINUM EXTENSION LADDERS WITH LEVELERS

ANSI I Load Capacity: 250 lbs		D1800-2EQ SERIES ALUMINUM EQUALIZER EXTENSION LADDER Exclusive ALFLO® rung joint means Twist-Proof® performance. Slip-resistant Traction-Tred® D-rungs. Factory installed adjustable EverLevel® leveling system exceeds OSHA and ANSI requirements. Easily adjustable in 3/8" increments up to 8-1/4". Dual action foot for use on hard or penetrable surfaces. Note: 16' Item 1FCF6 is not equipped with rope and pulley.	
----------------------------------	--	--	--

1FCF6	16 FT	Werner D1816-2EQ	Ladder Height 16', Maximum Working Length 13', Approx. Shipping Weight 31.5 lbs. (Does not include rope & pulley)
1FCF7	20 FT	Werner D1820-2EQ	Ladder Height 20', Maximum Working Length 17', Approx. Shipping Weight 37.5 lbs.
1FCF8	24 FT	Werner D1824-2EQ	Ladder Height 24', Maximum Working Length 21', Approx. Shipping Weight 45.5 lbs.
1FCF9	28 FT	Werner D1828-2EQ	Ladder Height 28', Maximum Working Length 25', Approx. Shipping Weight 56.0 lbs.



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

ALUMINUM EXTENSION LADDERS

ANSI IA Load Capacity: 300 lbs			D1500-2 SERIES EXTENSION LADDER Aluminum extension ladders with ALFLO® direct rung-to-rail connections for Twist-Proof® performance. Stacked rail design so base and fly are same width and separate easily for use as an extension or two single sections. Rugged shoe rests flat or is held in spur position with Shu-Lok® feature. Ladder is constructed with I-beam rails and mar-resistant end caps. Extruded aluminum gravity spring locks. Note: 16' Item 4XN89 is not equipped with rope and pulley.
4XN89	16 FT	Werner D1516-2	Ladder Height 16', Maximum Working Length 13', Approx. Shipping Weight 30.5 lbs.
4XN90	20 FT	Werner D1520-2	Ladder Height 20', Maximum Working Length 17', Approx. Shipping Weight 37.0 lbs.
4XN91	24 FT	Werner D1524-2	Ladder Height 24', Maximum Working Length 21', Approx. Shipping Weight 45.0 lbs.
4XN92	28 FT	Werner D1528-2	Ladder Height 28', Maximum Working Length 25', Approx. Shipping Weight 56.0 lbs.
4XN93	32 FT	Werner D1532-2	Ladder Height 32', Maximum Working Length 29', Approx. Shipping Weight 67.0 lbs.
4XN94	36 FT	Werner D1536-2	Ladder Height 36', Maximum Working Length 32', Approx. Shipping Weight 80.0 lbs.
4XN95	40 FT	Werner D1540-2	Ladder Height 40', Maximum Working Length 35', Approx. Shipping Weight 89.5 lbs.



FIBERGLASS LIGHTWEIGHT EXTENSION LADDERS

ANSI IAA Load Capacity: 375 lbs.			D7200-2 SERIES EXTENSION LADDER Lightweight Fiberglass Extension Ladder provides same duty rating but lighter carryweight. ALFLO® rung joints for Twist-Proof® performance. Rung plate connection for easy rung replacement. Slip-resistant Traction-Tred® D-Rungs. Combination shoes with slip-resistant rubber pads for hard surfaces or swivel the shoes to use spur plates for penetrable surfaces.
36FX58	16 FT	Werner D7216-2	Ladder Height 16', Maximum Working Length 13', Approx. Ship Weight 36 lbs.
36FX59	20 FT	Werner D7220-2	Ladder Height 20', Maximum Working Length 17', Approx. Ship Weight 44 lbs.
36FX60	24 FT	Werner D7224-2	Ladder Height 24', Maximum Working Length 21', Approx. Ship Weight 51 lbs.
36FX61	28 FT	Werner D7228-2	Ladder Height 28', Maximum Working Length 25', Approx. Ship Weight 58 lbs.
ANSI IA Load Capacity: 300 lbs			D6400-2 SERIES EXTENSION LADDER Lightweight Fiberglass Extension Ladder provides same duty rating but lighter carryweight. ALFLO® rung joints for Twist-Proof® performance. Direct Rung to Rail connections. Slip-resistant Traction-Tred® D-Rungs. Combination shoes with slip-resistant rubber pads for hard surfaces or swivel the shoes to use spur plates for penetrable surfaces.
36FX54	16 FT	Werner D6416-2	Ladder Height 16', Maximum Working Length 13', Approx. Ship Weight 32 lbs.
36FX55	20 FT	Werner D6420-2	Ladder Height 20', Maximum Working Length 17', Approx. Ship Weight 40 lbs.
36FX56	24 FT	Werner D6424-2	Ladder Height 24', Maximum Working Length 21', Approx. Ship Weight 46 lbs.
36FX57	28 FT	Werner D6428-2	Ladder Height 28', Maximum Working Length 25', Approx. Ship Weight 53 lbs.



Grainger item #	Height	Model #	Description
-----------------	--------	---------	-------------

FIBERGLASS EXTENSION LADDERS WITH LEVELERS

ANSI IAA Load Capacity: 375 lbs.			D7100-2LV SERIES EXTENSION LADDER Fiberglass D-rung extension ladder with rung plate rung-to-rail connections. Factory installed LeveLok® Levelers enable ladder to adapt to uneven terrain with simple foot action, Leveler extends up to 10" in 3/16" increments. Pre-pierced holes at top of ladder for easy field installation of accessories. Base and fly separate easily to use base section as single ladder. Ideal for utility and telecommunication industries.
3AZT2	20 FT	Werner D7120-2LV	Ladder Height 20', Approx. Shipping Weight 58.0 lbs. Maximum Working Length 17', Outside Shoe Base Width 22-3/4"
3AZT3	24 FT	Werner D7124-2LV	Ladder Height 24', Approx. Shipping Weight 66.5 lbs. Maximum Working Length 21', Outside Shoe Base Width 22-3/4"
3AZT4	28 FT	Werner D7128-2LV	Ladder Height 28', Approx. Shipping Weight 75.0 lbs. Maximum Working Length 25', Outside Shoe Base Width 22-3/4"



ALL FIBERGLASS EXTENSION LADDERS

ANSI IA Load Capacity: 300 lbs.			9500 FIBERMAX EXTENSION LADDER Fiberglass rungs connected to fiberglass box-beam rails. Rail and rung are connected with reinforced nylon plugs that interlock the entire system. Thick rubber treads and convenient spur plates.
3AZT5	16 FT	Werner 9516-2	Ladder Height 16', Approx. Shipping Weight 41.0 lbs. Maximum Working Length 13', Outside Shoe Base Width 18-3/8"
3AZT6	20 FT	Werner 9520-2	Ladder Height 20', Approx. Shipping Weight 49.0 lbs. Maximum Working Length 17', Outside Shoe Base Width 18-3/8"
3AZT7	24 FT	Werner 9524-2	Ladder Height 24', Approx. Shipping Weight 56.0 lbs. Maximum Working Length 21', Outside Shoe Base Width 18-3/8"
3AZT8	28 FT	Werner 9528-2	Ladder Height 28', Approx. Shipping Weight 64.0 lbs. Maximum Working Length 25', Outside Shoe Base Width 18-3/8"
3AZT9	32 FT	Werner 9532-2	Ladder Height 32', Approx. Shipping Weight 72.0 lbs. Maximum Working Length 29', Outside Shoe Base Width 18-3/8"



FIBERGLASS 3-SECTION COMPACT EXTENSION LADDERS

ANSI IA Load Capacity: 300 lbs.			D6200-3 SERIES FIBERGLASS COMPACT EXTENSION LADDER Innovative 3 section design reduces to shorter than standard 2 section design. Convenient to maneuver and carry around. Easy to transport on top of vehicles. ALFLO® rung joints for Twist-Proof® performance. Spring locks operate smoothly. Shoe with slip-resistant pad and spur plate. Retainer strap secures ladder for storage and transport. Note: 16' Item 22E977 is not equipped with rope and pulley.
22E977	16 FT	Werner D6216-3	Ladder Height 16', Total Length of sections 18', Maximum Working Length 13', Approx. shipping weight 40.5 lbs.
22E978	20 FT	Werner D6220-3	Ladder Height 20', Total Length of sections 23', Maximum Working Length 17', Approx. shipping weight 54 lbs.
22E979	24 FT	Werner D6224-3	Ladder Height 24', Total Length of sections 27', Maximum Working Length 21', Approx. shipping weight 61.0 lbs.
22E980	28 FT	Werner D6228-3	Ladder Height 28', Total Length of sections 31', Maximum Working Length 25', Approx. shipping weight 74.5 lbs.
22E981	32 FT	Werner D6232-3	Ladder Height 32', Total Length of sections 35', Maximum Working Length 29', Approx. shipping weight 81 lbs.



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

FIBERGLASS STRAIGHT LADDERS

ANSI IA Load Capacity: 300 lbs		D6200-1 SERIES FIBERGLASS STRAIGHT LADDERS ALFLO® rung joint means Twist-Proof® performance. Slip-resistant Traction-Tred® round rungs. Double rail shield bracket and shoe with Shu-Lok® slip-resistant pad and spur plate.	
2EJG2	8 FT	Werner D6208-1	Ladder Height 8', Base Width 19", Approx. Shipping Weight 19.5 lbs.
2EJG3	10 FT	Werner D6210-1	Ladder Height 10', Base Width 19", Approx. Shipping Weight 23.0 lbs.
2EJG4	12 FT	Werner D6212-1	Ladder Height 12', Base Width 19", Approx. Shipping Weight 27.0 lbs.
2EJG5	14 FT	Werner D6214-1	Ladder Height 14', Base Width 19", Approx. Shipping Weight 31.0 lbs.
2EJG6	16 FT	Werner D6216-1	Ladder Height 16', Base Width 19", Approx. Shipping Weight 37.0 lbs.
2EJG7	20 FT	Werner D6220-1	Ladder Height 20', Base Width 19", Approx. Shipping Weight 45.5 lbs.



ALUMINUM STRAIGHT LADDERS

ANSI IA Load Capacity: 300 lbs		D1500-1 SERIES SINGLE LADDER Aluminum single ladders with ALFLO® direct rung-to-rail connections for Twist-Proof® performance. Rugged shoe rests flat or is held in spur position with Shu-Lok® feature. Ladder is constructed with I-beam rails and mar-resistant end caps.	
3AZU7	8 FT	Werner D1508-1	Ladder Height 8', Approx. Shipping Weight 14.5 lbs. Base Width 18-1/8" outside rails
3AZU8	10 FT	Werner D1510-1	Ladder Height 10', Approx. Shipping Weight 17.5 lbs. Base Width 18-1/8" outside rails
3AZU9	12 FT	Werner D1512-1	Ladder Height 12', Approx. Shipping Weight 21.5 lbs. Base Width 18-1/8" outside rails
3AZV1	14 FT	Werner D1514-1	Ladder Height 14', Approx. Shipping Weight 27.0 lbs. Base Width 18-1/8" outside rails
3AZV2	16 FT	Werner D1516-1	Ladder Height 16', Approx. Shipping Weight 32.5 lbs. Base Width 18-1/8" outside rails
3AZV3	18 FT	Werner D1518-1	Ladder Height 18', Approx. Shipping Weight 38.5 lbs. Base Width 18-1/8" outside rails



FIBERGLASS MANHOLE LADDERS

ANSI IA Load Capacity: 300 lbs		M7100 SERIES MANHOLE LADDER Fiberglass straight ladders 12" wide. ALFLO® direct rung-to-rail connections for Twist-Proof® performance. Mar-resistant, vinyl coated aluminum hoop end caps for removing ladder from manhole. 3' replaceable plastic sleeves to avoid manhole rim damage to rail. Combination rail shield and shoe protects bottom of rail from damage.	
3AZV4	8 FT	Werner M7108-1	Ladder Height 8', Approx. Shipping Weight 20.0 lbs. Base Width 12-3/8"
3AZV5	10 FT	Werner M7110-1	Ladder Height 10', Approx. Shipping Weight 24.0 lbs. Base Width 12-3/8"
3AZV6	12 FT	Werner M7112-1	Ladder Height 12', Approx. Shipping Weight 28.0 lbs. Base Width 12-3/8"
3AZV7	14 FT	Werner M7114-1	Ladder Height 14', Approx. Shipping Weight 32.0 lbs. Base Width 12-3/8"
3AZV8	16 FT	Werner M7116-1	Ladder Height 16', Approx. Shipping Weight 39.5 lbs. Base Width 12-3/8"



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

STEP STOOLS

ANSI IA Load Capacity: 300 lbs		ALUMINUM AND FIBERGLASS STEP STOOLS	
-----------------------------------	--	-------------------------------------	--

4XN38	2 FT	Werner 150B	<p>Aluminum Step Stool Large molded top provides large standing platform. Molded vinyl foot pads riveted to rail. Spread 19". Width 17". Approx. Shipping Weight 5.5 lbs.</p>	
-------	------	-------------	--	--

3AZU6	2 FT	Werner 6202	<p>Fiberglass Step Stool Large molded top provides large standing platform. Combination rail end shield and foot with slip-resistant foot pad. Spread is 19-1/2". Width 17-1/4". Approx. Shipping Weight 9.0 lbs.</p>	
-------	------	-------------	--	--

4XP46	2 FT	Werner T372	<p>Aluminum Twin Step Stool 300 lbs. Duty Rating (per side) Designed for one or two person jobs. Ideal for use with stage planks. Folds to 7- 1/4" Wide. Base Spread 23-3/8". Bottom Width 21-1/4". Approx. Shipping Weight 9.0 lbs.</p>	
-------	------	-------------	---	--

4XP47	2 FT	Werner T6202	<p>Fiberglass Twin Step Stool 300 lbs. Duty Rating (per side) Designed for one or two person jobs. Ideal for use with stage planks. Folds to 7 1/2" Wide. Base Spread 23-3/8", Bottom Width 21-1/4". Approx. Shipping Weight 11.5 lbs.</p>	
-------	------	--------------	---	--

STEP STANDS

ANSI IAA Load Capacity: 375 lbs		ALUMINUM AND FIBERGLASS STEP STANDS Heavy duty 6" wide front rails and steps. Extra wide top. Spreader bars lock permanently open. Extra large feet for use on gratings.	
------------------------------------	--	---	--

5W216	2 FT	Werner SSA02	Aluminum. Ladder Height 2', Approx. Shipping Weight 16.0 lbs. Base Spread 21", Bottom Width 17"	
-------	------	--------------	---	--

6W705	3FT	Werner SSA03	Aluminum. Ladder Height 3'. Approx. Shipping Weight 21.0 lbs. Base Spread 27-1/2", Bottom Width 18-3/4"	
-------	-----	--------------	---	--

3LW39	22 FT	Werner SSF02	Fiberglass. Ladder Height 2'. Approx. Shipping Weight 15.0 lbs. Base Spread 21", Bottom Width 17"	
-------	-------	--------------	---	--

3LW40	33 FT	Werner SSF03	Fiberglass. Ladder Height 3'. Approx. Shipping Weight 19.5 lbs. Base Spread 27-1/2", Bottom Width 18-3/4"	
-------	-------	--------------	---	--

Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

PORTABLE WORK STANDS

ANSI IA Load Capacity: 300 lbs (per side)		ALUMINUM AND FIBERGLASS PORTABLE WORK STANDS 30" wide work stands with double wide top steps to provide wide platform. External Pinch-Proof™ spreaders for easy opening and closing. Mar-resistant feet for slip-resistance on concrete, wood and vinyl floors.	
---	--	---	--

3AZU1	2 FT	Werner TW372-30	Aluminum. Ladder Height 2'. Approx. Shipping Weight 12.5 lbs. Base Spread 22", Bottom Width 23"
--------------	-------------	------------------------	---

3AZU2	3 FT	Werner TW373-30	Aluminum. Ladder Height 3'. Approx. Shipping Weight 17.5 lbs. Base Spread 29", Bottom Width 34-3/4"
--------------	-------------	------------------------	---

3AZU3	4 FT	Werner TW374-30	Aluminum. Ladder Height 4'. Approx. Shipping Weight 24.0 lbs. Base Spread 36", Bottom Width 36-1/2"
--------------	-------------	------------------------	---

3AZU4	2 FT	Werner TW6202	Fiberglass. Ladder Height 2'. Approx. Shipping Weight 17.0 lbs. Base Spread 22-1/4", Bottom Width 31-1/4"
--------------	-------------	----------------------	---

3AZU5	3 FT	Werner TW6203	Fiberglass. Ladder Height 3'. Approx. Shipping Weight 24.0 lbs. Base Spread 29-3/4", Bottom Width 31-3/4"
--------------	-------------	----------------------	---



SCAFFOLDING

Aluminum and Steel Scaffolding			
---------------------------------------	--	--	--

4ZY17	4 FT	Werner PS-48	Rolling Portable Steel Scaffold Folds easily for storage and portability. Rolls easily on 4" non-marring hi-grade casters. Has 2 adjustable height planks. 500 lbs. Duty Rating (250 lbs. per plank).
--------------	-------------	---------------------	---



4XN62	6 FT	Werner 4101	Narrow Span 6' Adjustable Aluminum Base Section 6' Long x 29" Wide. Height adjusts from 6'6" to 7'6". Load Capacity 25 lbs. per square foot or 500 lbs. maximum per deck and scaffold. Includes walk board and 5" swivel locking casters.
--------------	-------------	--------------------	---



4XP11	6 FT	Werner 4110	Narrow Span 6' Aluminum Scaffold Guard Rail Section 6' Long x 29" Wide x 3-1/2' High.
--------------	-------------	--------------------	---



Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

SCAFFOLDING *continued*

Aluminum Scaffold Towers

4XP22	12 FT	Werner GW401	<p>12' HIGH ALUMINUM SCAFFOLD TOWER 6' Long x 29" Wide x 12' High Aluminum Scaffold Tower. Load Capacity 25 lbs. per square foot or 500 lbs. maximum per deck and scaffold. Includes walk board, 5" swivel locking casters, outriggers and toeboards.</p>	
-------	-------	--------------	---	--

4XP23	15 FT	Werner GW402	<p>15' HIGH ALUMINUM SCAFFOLD TOWER 6' Long x 29" Wide x 15' High Aluminum Scaffold Tower. Load Capacity 25 lbs. per square foot or 500 lbs. maximum per deck and scaffold. Includes walk board, 5" swivel locking casters, outriggers and toeboards.</p>	
-------	-------	--------------	---	--

4ZY18	20 Inches	Werner AP-20-MP6	<p>Aluminum Work Platform. 225 lbs. Load Capacity Portable and lightweight. Folds easily for storage. Highest Standing Level 20-9/16". Width 16-5/8", Length 40". Approx. Shipping Weight 75.0 lbs.(6)</p>	
-------	-----------	------------------	--	--

36FX62	21 Inches	Werner AP-30	<p>Pro Deck Aluminum Platform. 300 lbs. Load Capacity Extra large standing area with a rigid surface for working from side to side. The Pro Deck is ideal for working along walls and windows. Platform legs lock securely in place when in use and fold underneath platform for compact storage. The 300 lbs load capacity provides additional support for jobs requiring extra tools and supplies. Highest Standing Level 20-9/16". Width 16". Length 48". Approx. Shipping Weight 16.0 lbs.</p>	
--------	-----------	--------------	--	--

PLANKS

ANSI IA Load Capacity: 250 lbs (1 person)	<p>ALUMINUM EXTENSION PLANKS Planks are 14" Wide. For use on stepladders, telescoping multiladders, extension trestle ladders, and extension and single ladders equipped with ladder jacks.</p>		
--	---	--	--

4XP30	6 FT	Werner PA206	<p>Closed Position 6' Long. Extended Position 9' Long. Approx. Shipping Weight 31.0 lbs.</p>	
-------	------	--------------	--	--

4XP31	8 FT	Werner PA208	<p>Closed Position 8' Long. Extended Position 13' Long. Approx. Shipping Weight 40.5 lbs.</p>	
-------	------	--------------	---	--

4XP32	10 FT	Werner PA210	<p>Closed Position 10' Long. Extended Position 17' Long. Approx. Shipping Weight 56.5 lbs.</p>	
-------	-------	--------------	--	--

Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

STAGES, HANDRAILS AND TOEBOARDS

ALUMINUM STAGE PLANKS, HANDRAILS AND TOEBOARDS

See Red Book	8 - 39 FT	Varies by Size See Red Book	<p>Aluminum Stage Planks</p> <p>Ideal for ladder jack applications, swing stages, or catwalks. Strong design features double rungs on the ends for rigidity. Available in Lengths from 8' - 39' and Widths from 12" to 28". Load Capacity from 250 lbs. 1-Man to 750 lbs. 3-Man. Vinyl-coated end caps.</p>	

See Red Book	8 - 39 FT	Varies by Size See Red Book	<p>Modular Guard Rail and Toe Board Systems</p> <p>For use on Werner aluminum stage planks. Protects users and tools from falling off planks. Quick and easy to install, store and transport. Available in Lengths from 8' - 39' and Widths from 12" to 28". (Stage planks sold separately)</p>	

TRUCK RACK

Load Capacity: 1000 lbs Steel Over Cab Pickup Truck Rack

3AY77	Werner TR501-S	<p>Black. Approx. Shipping Weight 125 lbs. Vinyl protector strips to protect equipment against transit damage. Includes adaptor plates that allow rack to mount over most cabs (750 lbs. load capacity). Includes quick release rear bar feature and predrilled uprights. Cargo positioners help protect cargo in transit.</p>	
-------	----------------	--	--

VAN RACK

Load Capacity: 600 lbs Steel Van Rack

3AY76	Werner VR401-W	<p>White. Approx. Shipping Weight 40 lbs. Includes predrilled uprights. Cargo positions and vinyl strips help protect cargo in transit.</p>	
-------	----------------	---	--

Grainger Item #	Height	Model #	Description
-----------------	--------	---------	-------------

ACCESSORIES

Accessories designed to fit Werner ladders to increase productivity and safety

1XGF7		Werner AC50-JB-3	<p>JobBucket Accessory, 25 lbs. Load Capacity. Compatible with OBEL00, OBCN00, 6200 Series and 6000 Series. Increase ladder storage and maximize your work space on top of your ladder. Over 600 cubic inch capacity. Shipped in boxes of 3.</p> 
1XGF8		Werner AC58-TL	<p>ToolLasso® with Belt Clip Accessory Secures tools from falling. Can be wrapped around the grip of power tools, hand tools or caulk guns. Keeps tools within easy reach on top of your ladder or on a belt. Clip attaches to belt and ToolLasso® fits into belt clip.</p> 
4XN86		Werner AC19-2	<p>Extension Ladder Covers Helps protect surfaces from scratches and dents. Flexible and easy to install. Made of soft rubber material.</p> 
4XN88		Werner AC78	<p>QuickClick™ Stabilizer Stabilizer with spring-loaded locking latch makes it easier to install and remove than conventional stabilizers. Modular 3 component design allows for compact storage. Spans 44" and stands off 10".</p> 
4XN82		Werner AC10-20-02	<p>Aluminum Ladder Jacks Lightweight, sturdy and easy to use. Accepts planks up to 20" wide. Platform clamps secure entire ladder jack system. Jack mounts on either side of extension ladder. For use on ladders of 250 lbs., Type I Duty Rating or higher.</p> 
4ZY21		Werner PK70-1	<p>Aluminum Ladder Leveler Allows use on uneven surfaces and adjusts up to 8-1/2". Ladder Leveler with 2 base attachments. Base unit stays attached while leveler can be easily removed when not in use. Use on either side of ladder. For Werner extension ladders only.</p> 
4XN81		Werner 97P	<p>Stabilizer and Surface Protector Span adjustment is 49", 57" or 65". Stand-off distance is 12" or 29-1/2". Rectangular stabilizer spans double windows. Quickly converts stand off distance for larger overhangs. Mounts quickly and easily. Comes with rubber pads and fleece bonnets.</p> 

NOTE: SEE RED BOOK FOR ADDITIONAL ITEMS AND INFORMATION



www.wernerco.com

For more information contact your Grainger
Representative or visit Grainger.com®

AVAILABLE THROUGH

GRAINGER®

////// FOR THE ONES WHO GET IT DONE