



SOLUTIONS FOR A DROPS FREE ZONE.™

**THE COMPLETE GUIDE TO
OBJECTS AT HEIGHTS SAFETY.**



WWW.ERGODYNE.COM



PROUDLY SETTING A HIGHER STANDARD IN AT-HEIGHTS SAFETY

ANSI/ISEA 121 DROPPED OBJECTS STANDARD

We've teamed with the International Safety Equipment Association (ISEA) and a select few in the industry to release a new standard in at-heights safety — establishing minimum design, performance/testing and labeling requirements for equipment solutions that prevent dropped objects.

WHAT DOES THE DROPPED OBJECTS STANDARD COVER?



ANCHOR // TOOL ATTACHMENTS



TOOL TETHERS // LANYARDS



BUCKETS // CONTAINERS

278 DEATHS. OVER 52,000 INJURIES. AND NO TIME LEFT TO DELAY.

More and more workers are finding themselves ascending to heights in all industries, and along with them, the tools and equipment necessary to do the job. Join us in setting a higher standard in at-heights safety with innovative solutions, immersive education and a proactive game plan to stop drops and the damage done.

QUESTIONS

For questions about the ANSI/ISEA 121-2018 Dropped Objects Standard or how to design and implement a dropped objects program in your workplace, please call **800.225.8238**, email support@ergodyne.com or visit www.ergodyne.com.

A TOOL TETHERING KIT MADE FOR YOUR TRADE



It's all here – everything you need to tether the most common tools for the job, complete with simplified, step-by-step instructions. Gravity be warned. There's a new Drop Cop® in town. For full Squids® Tool Attachment and Tool Lanyard installation and user instructions, please refer to each product's individual instructions which can be found inside of the product packaging. For more detailed instructions, please refer to the product videos on www.ergodyne.com.



3183 CARPENTERS/LABORERS KIT

3183 // CARPENTERS/LABORERS KIT

ITEM # 19653



Tools to Tether:

- » Hard Hats
- » Gloves
- » Tape Measures
- » Claw/Sledge Hammers
- » Cordless Drills/Drivers
- » Adjustable Wrenches
- » Speed Squares
- » Pry Bars
- » Cats Paws
- » Pliers
- » Utility Knives
- » Torpedo Levels
- » Multi-Tool Scrapers
- » Jab Saws

Kit Includes:

- » 3713 Elastic Tool Tail™ (3)
- » 3700 Web Tool Tail™ (6)
- » 3755 Self-Adhering Tape Trap (2)
- » 3705 Wire Screwgate Tool Tail™ (6)
- » 3770L Tape Measure Trap (1)
- » 3780L Power Tool Trap™ (1)
- » 3156 Coil Tool Lanyard (2)
- » 3118F(x) Tool Lanyard (1)
- » 3108F(x) Tool Lanyard (1)
- » 3400 Grabber - Dual Clip (1)

3184 // FINISHERS/MASONS KIT

ITEM # 19654



Tools to Tether:

- » Hard Hats
- » Gloves
- » Tape Measures
- » Claw/Sledge Hammers
- » Grinders
- » Pliers
- » Utility Knives
- » Margin/Mason Trowels
- » Floats/Edgers/ Mag Trowels

Kit Includes:

- » 3713 Elastic Tool Tail™ (3)
- » 3700 Web Tool Tail™ (6)
- » 3755 Self-Adhering Tape Trap (2)
- » 3797 Power Tool Trap™ - Grinder (1)
- » 3770L Tape Measure Trap (1)
- » 3156 Coil Tool Lanyard (2)
- » 3118F(x) Tool Lanyard (1)
- » 3108F(x) Tool Lanyard (1)
- » 3400 Grabber - Dual Clip (1)

3185 // GLAZIERS KIT

ITEM # 19655



Tools to Tether:

- » Hard Hats
- » Gloves
- » Tape Measures
- » Cordless Drills/Drivers
- » Pliers
- » Utility Knives
- » 8" Flat Bars
- » Spray Bottles
- » Caulking Knives

Kit Includes:

- » 3713 Elastic Tool Tail™ (3)
- » 3700 Web Tool Tail™ (6)
- » 3755 Self-Adhering Tape Trap (1)
- » 3704 Wire Loop Tool Tail™ (6)
- » 3780L Power Tool Trap™ (1)
- » 3755 Water Bottle/Canister Trap (1)
- » 3770L Tape Measure Trap (1)
- » 3156 Coil Tool Lanyard (2)
- » 3118F(x) Tool Lanyard (1)
- » 3108F(x) Tool Lanyard (1)
- » 3400 Grabber - Dual Clip (1)

3186 // IRON

ITEM # 19656



Tools to Tether:

- » Hard Hats
- » Gloves
- » Tape Measures
- » Claw/Sledge Hammers
- » Cordless Drills/D
- » Sleever Bars
- » Pliers
- » Spud Wrenches
- » Folding Tape Mea
- » Bolt Cutters

3187 // SCA

ITEM # 19657



Tools to Tether:

- » Hard Hats
- » Gloves
- » Tape Measures
- » Claw/Sledge Hammers
- » Mallets
- » Adjustable Wren
- » Scaffolders 3-in
- » Nips
- » Levels



GET YOUR KIT TOGETHER MORE TOOL SPECIFIC KITS

Maybe you don't need the full-on safety smorgasbord of our Trades Tethering Kits. NBD. Help yourself to our à la carte kit offering of individual, tool-specific tethering kits – complete with everything you need to tether one type of tool.

N/STEEL WORKERS KIT

Kit Includes:

- » 3713 Elastic Tool Tail™ (6)
- » 3700 Web Tool Tail™ (6)
- » 3755 Self-Adhering Tape Trap (2)
- » 3790XL Shackle Trap (2)
- » 3770L Tape Measure Trap (1)
- » 3780L Power Tool Trap™ (1)
- » 3156 Coil Tool Lanyard (2)
- » 3118F(x) Tool Lanyard (1)
- » 3108F(x) Tool Lanyard (1)
- » 3400 Grabber - Dual Clip (1)

FFOLDERS KIT

Kit Includes:

- » 3713 Elastic Tool Tail™ (6)
- » 3700 Web Tool Tail™ (6)
- » 3755 Self-Adhering Tape Trap (2)
- » 3790XL Shackle Trap (2)
- » 3770L Tape Measure Trap (1)
- » 3156 Coil Tool Lanyard (2)
- » 3118F(x) Tool Lanyard (1)
- » 3108F(x) Tool Lanyard (1)
- » 3400 Grabber - Dual Clip (1)



3180 // 2LB / 0.9KG TOOL TETHERING KIT

ITEM # 19650

Tether up to six 2lb / 0.9kg tools

Includes:

- » 3700 Web Tool Tail™ (6)
- » 3755 Self-Adhering Tape Trap (1)
- » 3130S Coil Tool Lanyard (1)



3181 // 5LB / 2.3KG TOOL TETHERING KIT

ITEM # 19651

Tether up to four 5lb / 2.3kg tools

Includes:

- » 3103 Detachable Loops (3)
- » 3755 Self-Adhering Tape Trap (1)
- » 3102F(x) Tool Lanyard - Modular (1)



3182 // 10LB / 4.5KG TOOL TETHERING KIT

ITEM # 19652

Tether up to three 10lb / 4.5kg tools

Includes:

- » 3713 Elastic Loop Tool Tail™ (3)
- » 3755 Self-Adhering Tape Trap (1)
- » 3100F(x) Tool Lanyard (1)



3190 // TAPE MEASURE TETHERING KIT

ITEM # 19660

Tether one standard tape measure

Includes:

- » 3770L Tape Measure Trap (1)
- » 3130S Coil Tool Lanyard (1)



3191 // POWER TOOL TETHERING KIT

ITEM # 19661

Tether one standard cordless power tool

Includes:

- » 3780L Power Tool Trap (1)
- » 3100F(x) Tool Lanyard (1)



3192 // 3LB / 1.4KG WRIST LANYARD TETHERING KIT

ITEM # 19662

Tether up to four 3lb / 1.4kg tools

Includes:

- » 3103 Detachable Loops (3)
- » 3755 Self-Adhering Tape Trap (2)
- » 3116 Wrist Lanyard - Buckle (1)



3193 // TAPE MEASURE TETHERING KIT

ITEM # 19663

Tether one standard tape measure

Includes:

- » 3770L Tape Measure Trap (1)
- » 3100F(x) Tool Lanyard (1)



3194 // HAND TOOL TETHERING KIT

ITEM # 19664

Tether up to four screwdrivers/hex keys

Includes:

- » 3740 Hand Tool Trap™ - Slips® (4 - variety)
- » 3156 Coil Tool Lanyard (1)



3195 // CELLPHONE TETHERING KIT

ITEM # 19665

Tether one plus size phone

Includes:

- » 3760 Cellphone Trap - Sleeve Plus (1)
- » 3156 Coil Tool Lanyard (1)



3196 // GRINDER TETHERING KIT

ITEM # 19666

Tether one standard grinder

Includes:

- » 3797 Power Tool Trap™ - Grinder (1)
- » 3110F(x) Tool Lanyard (1)



**PLAN YOUR WORK.
WORK YOUR PLAN.**



THE ANATOMY OF AWESOMENESS:

THIRD-PARTY CERTIFIED WEIGHT RATINGS

SECURE HARDWARE

DURABLE SYNTHETIC MATERIALS

RETROFIT CONNECTOR VARIETY

FUNCTIONAL MATERIALS AND DESIGNS



ANSI COMPATIBLE	OSHA	SAFETY	3770	ORDER MULTIPLE 1
-----------------	------	--------	-------------	----------------------------

TAPE MEASURE TRAP

MAXIMUM LOAD LIMIT
**2 LBS
.9 KG**

ANSI/ISEA
121

ITEM #	SIZE	COLOR
19770	L	Orange
19771	XL	Black

// PATENTED

ANSI COMPATIBLE	OSHA	SAFETY	3740	ORDER MULTIPLE 1
-----------------	------	--------	-------------	----------------------------

HAND TOOL TRAP™ - SLIPS®

AVAILABLE IN FOUR SIZES

TETHER UP TO

MAXIMUM LOAD LIMIT
**1 LB
.5 KG**

ANSI/ISEA
121

ITEM #	SIZE	COLOR
19740	S	Black - Four Pack
19741	M	Black - Four Pack
19742	L	Black - Four Pack
19743	XL	Black - Four Pack
19940-BULK	S	Black - Sixty Pack
19941-BULK	M	Black - Sixty Pack
19942-BULK	L	Black - Sixty Pack
19943-BULK	XL	Black - Sixty Pack
19744	Variety	Black - 4 Sizes

// PATENTED

ANSI COMPATIBLE	3704/3705	ORDER MULTIPLE 1
-----------------	------------------	----------------------------

WIRE TOOL TAILS

MAXIMUM LOAD LIMIT
**3 LBS
1.4 KG**

ANSI/ISEA
121

3705

3704

MAXIMUM LOAD LIMIT
**2 LBS
.9 KG**

ANSI/ISEA
121

ITEM #	COLOR	ITEM #	COLOR
3704	Orange - Six Pack	3705	Orange - Six Pack
19707	Orange - Six Pack	19709	Orange - Six Pack

ANSI COMPATIBLE	OSHA	SAFETY	3780	ORDER MULTIPLE 1
-----------------	------	--------	-------------	----------------------------

POWER TOOL TRAP™

MAXIMUM LOAD LIMIT
**6 LBS
2.7 KG**

MAXIMUM LOAD LIMIT
**10 LBS
4.5 KG**

ANSI/ISEA
121

ITEM #	SIZE	COLOR
19782	S	Black
19784	L	Black

// PATENTED

ANSI  **3760** ORDER MULTIPLE **1**

CELL PHONE TRAP - SLEEVE

MAXIMUM LOAD LIMIT
1 LB
.5 KG



ANSI/ISEA
121

ITEM #	SIZE	COLOR
19762	Standard	Clear
19763	Plus	Clear

// PATENT PENDING

ANSI  **3765** ORDER MULTIPLE **1**

TABLET TRAP - SLEEVE

MAXIMUM LOAD LIMIT
2 LBS
.9 KG



ANSI/ISEA
121

ITEM #	SIZE	COLOR
19764	Standard	Clear

// PATENT PENDING

ANSI  **3775** ORDER MULTIPLE **1**

WATER BOTTLE/CANISTER TRAP - SLEEVE

MAXIMUM LOAD LIMIT
2 LBS
.9 KG

MAXIMUM LOAD LIMIT
3 LBS
1.4 KG



ANSI/ISEA
121

ITEM #	SIZE	COLOR
19775	S	Black
19776	L	Black

ANSI  **3796** ORDER MULTIPLE **1**

POWER TOOL TRAP™ - DRILL/IMPACT BRACKET

MAXIMUM LOAD LIMIT
3 LBS
1.4 KG



ANSI/ISEA
121

MODEL #3796

MAX CAPACITY: 3.5 LBS / 1.6 KG
ITEM # 19796
ITEM # 19797

ITEM #	SIZE	COLOR
19796	—	Stainless

// PATENTED

ANSI  **3797** ORDER MULTIPLE **1**

POWER TOOL TRAP™ - GRINDER BRACKET

MAXIMUM LOAD LIMIT
8 LBS
3.6 KG



ANSI/ISEA
121

MODEL #3797

ITEM #	SIZE	COLOR
19797	—	Stainless

// PATENTED

ANSI  **3798** ORDER MULTIPLE **1**

POWER TOOL TRAP™ - PNEUMATIC BRACKET

MAXIMUM LOAD LIMIT
5 LBS
2.3 KG



ANSI/ISEA
121

MODEL #3798
ITEM # 19798

ITEM #	SIZE	COLOR
19798	—	Stainless


// PATENTED

KNOW YOUR TOOL TYPES


HAND TOOLS



POWER TOOLS



INSTRUMENTS



OTHER



ANSI **3755** ORDER MULTIPLE **1**

SELF-ADHERING TAPE TRAP

MAXIMUM LOAD LIMIT
15 LBS
6.8 KG

ANSI/ISEA 121

• Compatible with tails 3700, 3703, 3713, 3103

ITEM #	SIZE	COLOR
19755	1" (2.5cm) x 12ft (365.8cm)	Gray
19756	1" (2.5cm) x 12ft (365.8cm)	Orange

3723/3724/3726 ORDER MULTIPLE **1**

COLD SHRINK TRAP

MAXIMUM LOAD LIMIT
5 LBS
2.3 KG

MAXIMUM LOAD LIMIT
10 LBS
4.5 KG

MAXIMUM LOAD LIMIT
15 LBS
6.8 KG

ANSI/ISEA 121

AVAILABLE IN THREE SIZES

• Compatible with tails 3703, 3713, 3103

3723:		3724:		3726:	
ITEM #	SIZE	ITEM #	SIZE	ITEM #	SIZE
19723	3" (7.6cm)	19724	4" (10.2cm)	19726	6" (15.3cm)

PATENTED

ANSI **3790** ORDER MULTIPLE **1**

SHACKLE TRAPS

MAXIMUM LOAD LIMIT
15 LBS
6.8 KG

ANSI/ISEA 121

PACKAGED (2) PER PACK

ITEM #	SIZE	COLOR
19792	S	Stainless Steel
19793	M	Stainless Steel
19794	L	Stainless Steel
19795	XL	Stainless Steel

ANSI **3103/3703/3713** ORDER MULTIPLE **6**

ELASTIC TOOL TAILS™

ANSI/ISEA 121

3703 3703EXT 3103 3175

MAXIMUM LOAD LIMIT
10 LBS
4.5 KG

MAXIMUM LOAD LIMIT
15 LBS
6.8 KG

MAXIMUM LOAD LIMIT
5 LBS
2.3 KG

MAXIMUM LOAD LIMIT
40 LBS
18 KG

3703:

3 PACK ITEM #	60 PACK ITEM #	SIZE	COLOR
19767	19767-Bulk	Std.	HV Lime
19769	—	Ext.	HV Lime

3713: W/ SWIVEL

3 PACK ITEM #	60 PACK ITEM #	SIZE	COLOR
19765	19765-Bulk	Std.	HV Lime

3103: LANYARDS

3 PACK ITEM #	60 PACK ITEM #	SIZE	COLOR
19068	—	Std.	Black
19069	—	Std.	HV Lime

3175: ANCHOR & TOOL TAIL

ITEM #	SIZE	COLOR
19175	—	Black

ANSI **3700** ORDER MULTIPLE **6**

WEB TOOL TAILS™


MAXIMUM LOAD LIMIT
2 LBS
.9 KG

ANSI/ISEA 121

PACKAGED (6) PER PACK

• Compatible with trap 3755

6 PACK ITEM #	60 PACK ITEM #	SIZE	COLOR
19703	19703-Bulk	3.5" (9.0cm)	Black
19704	19704-Bulk	4.5" (11.5cm)	Orange
19705	19705-Bulk	5.5" (14.0cm)	Black
19701	—	Variety Pack	Blk/Org



3010

ORDER MULTIPLE
1

RETRACTABLE TOOL LANYARD - SINGLE CARABINER WITH BELT SLOT



MAXIMUM LOAD LIMIT
5 LBS
2.3 KG

ANSI/ISEA
121

ITEM #	SIZE	STYLE	COLOR
19310	48" (123cm)	Single Carabiner	Black

3002

ORDER MULTIPLE
1

LOW PROFILE RETRACTABLE TOOL LANYARD - BELT LOOP



MAXIMUM LOAD LIMIT
2 LBS
.9 KG

ANSI/ISEA
121

ITEM #	SIZE	STYLE	COLOR
19302	48" (123cm)	Single Carabiner	Black

// PATENT PENDING

3000/3001

ORDER MULTIPLE
1

RETRACTABLE TOOL LANYARD



MAXIMUM LOAD LIMIT
1 LB
.5 KG

ANSI/ISEA
121

MAXIMUM LOAD LIMIT
2 LBS
.9 KG

ANSI/ISEA
121

ITEM #	SIZE	STYLE	COLOR
19300	48" (123cm)	Dual Carabiner	Black
19301	48" (123cm)	Single Carabiner	Black

// PATENTED

3011

ORDER MULTIPLE
1

RETRACTABLE TOOL LANYARD - DUAL CARABINER



MAXIMUM LOAD LIMIT
8 LBS
3.6 KG

ANSI/ISEA
121

ITEM #	SIZE	STYLE	COLOR
19311	48" (123cm)	Dual Carabiner	Black

3003

ORDER MULTIPLE
1

LOW PROFILE RETRACTABLE TOOL LANYARD - DUAL CARABINER



MAXIMUM LOAD LIMIT
2 LBS
.9 KG

ANSI/ISEA
121

ITEM #	SIZE	STYLE	COLOR
19303	48" (123cm)	Dual Carabiner	Black

// PATENT PENDING

3025/3026

ORDER MULTIPLE
1

RETRACTABLE TOOL TAILS™



MAXIMUM LOAD LIMIT
1 LB
.5 KG

3025

MAXIMUM LOAD LIMIT
2 LBS
.9 KG

3026

3025: TAILS (3 PK.)

ITEM #	COLOR
19325	Black

3026: TAILS (3 PK.)

ITEM #	COLOR
19326	Black

		<h1>3101_{F(x)}</h1>	ORDER MULTIPLE 6
SINGLE STAINLESS STEEL CARABINER TOOL LANYARD			
ITEM #	SIZE	COLOR	
19803	Std. 38" - 48" (96cm - 122cm)	Orange & Gray	
// PATENTED			

		<h1>3108_{F(x)}</h1>	ORDER MULTIPLE 6
SINGLE LOCKING CARABINER TOOL LANYARD			
ITEM #	SIZE	COLOR	
19808	Std. 38" - 48" (96cm - 122cm)	Orange & Gray	
// PATENTED			

		<h1>3109_{F(x)}</h1>	ORDER MULTIPLE 6
TOOL LANYARD SINGLE SWIVELING LOCKING CARABINER			
ITEM #	SIZE	COLOR	
19809	Std. 38" - 48" (96cm - 122cm)	Orange & Gray	
// PATENTED			

		<h1>3111_{F(x)}</h1>	ORDER MULTIPLE 6
DUAL STAINLESS STEEL CARABINER TOOL LANYARD			
ITEM #	SIZE	COLOR	
10823	Std. 38" - 48" (96cm - 122cm)	Orange & Gray	
// PATENTED			

		<h1>3118_{F(x)}</h1>	ORDER MULTIPLE 6
DUAL LOCKING CARABINER TOOL LANYARD			
ITEM #	SIZE	COLOR	
19828	Std. 38" - 48" (96cm - 122cm)	Orange & Gray	
// PATENTED			

		<h1>3119_{F(x)}</h1>	ORDER MULTIPLE 6
TOOL LANYARD DUAL SWIVELING LOCKING CARABINER			
ITEM #	SIZE	COLOR	
19829	Std. 38" - 48" (96cm - 122cm)	Orange & Gray	
// PATENTED			



3101/3111

ORDER MULTIPLE
6

SS SCREWGATE CARABINER LANYARD - SINGLE AND DUAL



3101

ITEM #	SIZE	COLOR
19007	Std. 35" - 42" (89cm - 110cm)	HV Lime
19017	Ext. 42" - 54" (110cm - 140cm)	HV Lime

3111

ITEM #	SIZE	COLOR
19027	Std. 35" - 42" (89cm - 110cm)	HV Lime
19037	Ext. 42" - 54" (110cm - 140cm)	HV Lime

3129/3139

ORDER MULTIPLE
1

40LB. HEAVY-DUTY LANYARDS



3129: SINGLE CARABINER

ITEM #	SIZE	COLOR
19137	76" (193cm)	Black

3139: DUAL CARABINER

ITEM #	SIZE	COLOR
19139	76" (193cm)	Black



3114/3116



ORDER MULTIPLE
6

PULL-ON WRIST TOOL LANYARD - CARABINER/BUCKLE



ITEM #	STYLE	COLOR
19056	Carabiner	Black
10957	Buckle	Black

// PATENTED



3311

ORDER MULTIPLE
1

SS SCREWGATE TRIPLE CARABINER - TWIN LEG



ITEM #	SIZE	COLOR
19083	Std. 35" - 42" (89cm - 110cm)	HV Lime

3148/3149

ORDER MULTIPLE
1

80LB. HEAVY-DUTY LANYARDS



3148: SINGLE CARABINER

ITEM #	SIZE	COLOR
19148	76" (193cm)	Orange

3149: DUAL CARABINER

ITEM #	SIZE	COLOR
19149	76" (193cm)	Orange



3115

ORDER MULTIPLE
6

WRIST TOOL LANYARD



ITEM #	SIZE	COLOR
19042	S/M	Black
19052	L/XL	Black



3150/3155

ORDER MULTIPLE 6

ELASTIC HARD HAT LANYARD - BUCKLE OR CLAMP



3157: BUCKLE

ITEM #	SIZE	COLOR
19150	21.5"	HV Lime

3158: CLAMP

ITEM #	SIZE	COLOR
19155	23"	HV Lime



3130

ORDER MULTIPLE 6

COIL TOOL LANYARD



ITEM #	SIZE	COLOR
19130	Small	HV Lime
19131	Medium	Orange

// PATENTED

3420

ORDER MULTIPLE 6

GLOVE CLIP - SWIVELING DUAL CLIP MOUNT



ITEM #	COLOR
19412	Black
19417	Blue
19418	HV Orange
19419	HV Lime
19413	Red
19415	Granite

// PATENT PENDING

3157/3158

ORDER MULTIPLE 6

COIL HARD HAT LANYARD - BUCKLE OR CLAMP



3157: BUCKLE

ITEM #	SIZE	COLOR
19156	18"	Black
19157	18"	HV Lime

3158: CLAMP

ITEM #	SIZE	COLOR
19158	18"	Black
19158	18"	HV Lime

3156/3166

ORDER MULTIPLE 6

COIL TOOL LANYARD



ITEM #	SIZE	CARABINER	COLOR
19161	12"-48" (30.5cm - 123cm)	Single	Gray
19162	12"-48" (30.5cm - 123cm)	Dual	Gray

3400/3405

ORDER MULTIPLE 6

GLOVE CLIP - DUAL OR BELT CLIP MOUNT



3400: DUAL CLIP

ITEM #	COLOR
19112	Black
19117	Blue
19118	HV Orange
19119	HV Lime
19113	Red
19115	Granite

3405: BELT CLIP

ITEM #	COLOR
19129	Black
19127	Blue
19128	HV Orange
19129	HV Lime
19123	Red
19125	Granite


// PATENTED

KNOW YOUR TOOL TYPES


HAND TOOLS



POWER TOOLS



INSTRUMENTS



OTHER



HEAVY-GAUGE STITCHING

THIRD-PARTY CERTIFIED TO A 5:1 SAFETY FACTOR

PATENTED SAFETY TOP

5960T

DURABLE FABRICS

REINFORCED BOTTOM

* Note: lanyards and tools not included... Duh!



5940

ORDER MULTIPLE 1

CANVAS BUCKET - SWIVELING CARABINER



SWIVEL CARABINER

ITEM #	SIZE	COLOR
14940	L	Gray

SWIVEL CARABINER W/TOP

ITEM #	SIZE	COLOR
14840	L	Gray

// PATENTED



5930

ORDER MULTIPLE 1

CANVAS BUCKET



WEB HANDLE

ITEM #	SIZE	COLOR
14930	L	Gray

WEB HANDLE W/TOP

ITEM #	SIZE	COLOR
14830	L	Gray

// PATENTED

5945 ORDER MULTIPLE 1

XL CANVAS BUCKET - SWIVELING CARABINER

150 LBS 58 KG



XL SWIVEL CARABINER **XL SWIVEL CARABINER W/TOP**

ITEM #	SIZE	COLOR
14945	XL	Gray
14845	XL	Gray

// PATENTED

5970 ORDER MULTIPLE 1

POLYESTER BUCKET - SWIVELING HOOK

100 LBS 45 KG



SWIVEL SNAP **SWIVEL SNAP W/TOP**

ITEM #	SIZE	COLOR
14970	L	Black
14870	L	Black

// PATENTED

5960 ORDER MULTIPLE 1

CANVAS BUCKET D-RINGS

150 LBS 58 KG

TETHER CAPACITY

20 LBS 9.1 KG



WEB HANDLE W/D-RINGS **WEB D-RINGS W/TOP**

ITEM #	SIZE	COLOR
14960	L	Gray
14860	L	Gray

// PATENTED

5935 ORDER MULTIPLE 1

XL-CANVAS BUCKET

150 LBS 58 KG



XL WEB HANDLE **XL WEB HANDLE W/TOP**

ITEM #	SIZE	COLOR
14935	XL	Gray
14835	XL	Gray

// PATENTED

5975 ORDER MULTIPLE 1

POLYESTER BUCKET

100 LBS 45 KG



WEB HANDLE **WEB HANDLE W/TOP**

ITEM #	SIZE	COLOR
14975	L	Black
14875	L	Black

// PATENTED

5937/5938 ORDER MULTIPLE 1

BUCKET SAFETY TOP - POLYESTER



5937



5938

ITEM #	SIZE	COLOR
14938	12.5" D (32cm)	Black
14937	16.5" D (41cm)	Black



HEAVY-DUTY ZIPPERS

BALLISTIC FABRICS



REINFORCED BASE

VARIETY OF POCKETS

D-RINGS FOR TOOL LANYARD



5843

ORDER MULTIPLE
1

TOOL BACKPACK

MAXIMUM LOAD LIMIT
**50 LBS
22.6 KG**



• 13.5"L x 8.5"W x 18"H (34cm x 22cm x 61cm)

ITEM #	SIZE	COLOR
19321	—	Black

	5561	ORDER MULTIPLE 1
SMALL TOOL & RADIO HOLSTER		
<ul style="list-style-type: none"> • 1680D ballistic polyester • Holds radios, pliers, and other hand tools • Two D-rings for tool lanyard attachment • Straps designed for quick attachment and removal • 4.5"L x 2.5"W x 8.5"H (11cm x 6cm x 22cm) 		
ITEM #	SIZE	COLOR
13561	—	Gray
// PATENTED		


	5562	ORDER MULTIPLE 1
HAMMER HOLSTER		
<ul style="list-style-type: none"> • 1680D ballistic polyester • Holds standard hammers and sledges • Two D-rings for tool lanyard attachment • Straps designed for quick attachment and removal • 6"L x 3"W x 8"H (15cm x 8cm x 20cm) 		
ITEM #	SIZE	COLOR
13662	—	Gray
// PATENTED		

	5528	ORDER MULTIPLE 1
TOPPED PARTS POUCH		
<ul style="list-style-type: none"> • 7.5"L x 7.5"W x 12"H (19cm x 19cm x 30cm) 		
ITEM #	SIZE	COLOR
13628	—	Black
// PATENTED		

	5517/5527	ORDER MULTIPLE 1
PREMIUM TOPPED PARTS POUCHES		
5517	5527	
<ul style="list-style-type: none"> • 1680D ballistic polyester • Snap-hinge closure for safety and security • Two exterior D-rings for tool lanyard attachment • Straps designed for quick attachment and removal • 10"L x 6"W x 11.5"H (25cm x 15cm x 29cm) 		
ITEM #	SIZE	CLOSURE
13627	—	Hinge Top
13647	—	Zipper Top
// PATENTED		

	5725/5728	ORDER MULTIPLE 1
TOPPED BOLT BAG AND TALL TOPPED BOLT BAG		
5725	5728	
<ul style="list-style-type: none"> • 10"L x 5"W x 9"H (25cm x 13cm x 23cm) • 10"L x 5"W x 13"H (25cm x 13cm x 33cm) 		
STANDARD		TALL
ITEM #	SIZE	COLOR
14425	—	White
14428	—	White
// PATENTED		

	5538	ORDER MULTIPLE 1
TOPPED PARTS POUCH		
<ul style="list-style-type: none"> • 7.5"L x 7.5"W x 12"H (19cm x 19cm x 30cm) 		
ITEM #	SIZE	COLOR
13638	—	Orange
// PATENTED		



GRAVITY HURTS

// OBJECTS AT HEIGHTS SAFETY SOLUTIONS //



TENACIOUS SINCE 1983.

**INTERGALACTIC HEADQUARTERS: 44° 58' 18.31" N 93° 09' 12.88" W ALT. 934 FT.
1021 BANDANA BOULEVARD EAST SUITE 220 SAINT PAUL, MN, USA 55108
PHONE 651 642 9889 // 800 225 8238 WWW.ERGODYNE.COM**

©2020 Ergodyne. All Rights Reserved. All Wrongs Reversed. Ergodyne, Ergoman and Ergoman design, Tenacious Work Gear Logo, Ergodyne Tenacious Work Gear, Arsenal, Chill-Its, GloWear, Nu²O₂, Squids, Sticky Fingers, ProFlex, CORE Performance Work Wear, N-Ferno and SHAX are registered trademarks of Ergodyne and protected in the U.S. and abroad. Be Tenacious, BET (Beverage Extrication Tool), Open-Center Stay, Perfor-air, Power Panel Positioner, Storm Drains, Products for Occupational Athletes, Trex, Hot Rox, Tenacious-U, and ZeroRebound, Lil' Buddies, Skullerz and Tenacious Testers are trademarks of Ergodyne. Trademarks of companies mentioned herein appear for identification purposes only and are the property of their respective companies. All other product names mentioned herein may be trademarks and/or registered trademarks of their respective owners. Ergodyne is a division of Tenacious Holdings Inc.