

SAFETY TRACK®

NON-SLIP TAPES AND TREADS

Category Grit

Non-slip grit tapes and treads for use in commercial, heavy duty, and military grades for high slip resistance indoors and outdoors.



Safety Track® Commercial – 3100

Non-slip 80 grit tapes and treads help prevent slips on floors, stairs, ramps, and sports equipment. This product has been engineered to exceed OSHA standards by providing a durable, consistent, non-slip surface. Available in a wide range of tape widths and tread sizes and can be laser cut into any shape.



Safety Track® Heavy Duty – 3200

Non-slip 46 grit tapes and treads stand up to the oil, diesel fuel, and mud found in the most extreme conditions in mining, refining, agriculture, manufacturing, construction, and many other industries. This product delivers a consistent, long-lasting “high slip resistance” performance under the toughest conditions. Available in a wide range of tape widths and tread sizes and can be laser cut into any shape.



Safety Track® Commercial Color – 3300

Non-slip 60 grit tapes and treads have been designed for general purpose applications. Products come in a range of colors including hazard striped message treads and popular safety yellow, red, and orange, among others. Available in a wide range of tape widths and tread sizes and can be laser cut into any shape.



SAFETY TRACK®

NON-SLIP TAPES AND TREADS


Category Grit

Non-slip grit tapes and treads for use in commercial, heavy duty, and military grades for high slip resistance indoors and outdoors.



Safety Track® Glo Brite® Photoluminescent 3400

Photoluminescent non-slip egress tapes and treads glow to show the way out in the event of a sudden power outage. These tapes reduce the risk of slips and falls and are designed for marking stairs and corridors as part of an emergency egress route. They meet rigid ASTM and NYC (MEA #235-05-M) standards. Available in a wide range of tape widths and tread sizes and can be laser cut into any shape.



Safety Track® Conformable 3700

Conformable 60 grit tapes and treads are foil backed and conform to irregular surfaces like radius corners, bends, ladder stairs, diamond tread plate, and other deeply textured surfaces. Designed for heavy traffic in tough environments, these tapes and treads have excellent stability in high and low temperature ranges. Available in a wide range of tape widths and tread sizes and can be laser cut into any shape.



Safety Track® Military Grade 3800

Military Grade peel-and-stick 36 grit tapes and treads are approved by NAVSEA under MIL-PRF-24667C Type XI. With a very heavy grit designed for decks of vessels used by the U.S. Navy, U.S. Coast Guard, and U.S. Marine Corps, Jessup's Military Grade products stand up to harsh marine environments, equipment abrasions, heavy traffic, and temperature fluctuations. Available in a wide range of tape widths and tread sizes and can be laser cut into any shape.

