



MCR
SAFETY

N9690FC

Ninja

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. The Ninja® Ice Fully Coated gloves features a 15 gauge black nylon shell with a 7 gauge acrylic terry interior liner. Black HPT fully coated glove.

FEATURES:

- Acrylic Terry liner for insulation / warmth.
- Black HPT repels liquids while providing strong wet or dry grip
- Fully coated for maximum protection
- Coating remains soft in temperatures as low as -58 F

APPLICATIONS:

Cold storage applications, Commercial fishing, Frozen food packaging, Agriculture, Construction, Material Handling



TECHNICAL DATA FOR: N9690FC

| | | | |
|-----------------------|-----------------|-------------------------------------|------------------------------------------------|
| Series | Ninja | EN 388 : CE Score - Abrasion | 3 |
| Material Group | Strings | EN 388 : CE Score - Cut | 2 |
| Product Type | Dipped | EN 388 : CE Score - Tear | 3 |
| Glove Size | Large | EN 388 : CE Score - Puncture | 2 |
| Gauge | 15 / 7 Gauge | ANSI Cut | ANSI Cut A3 |
| Material | Nylon / Acrylic | ANSI Puncture | ANSI Puncture 2 |
| Insulated | Insulated | ANSI Abrasion | ANSI Abrasion 3 |
| Lining | Acrylic | ANSI Contact Heat | Level 2 (Applications less than 284 degrees F) |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved




MCR
SAFETY

N9690FC

Ninja

Dipped

Specification Sheet



| Item No: | Size: | A: | B: | C: | Case Weight | UOM Weight |
|------------|------------|--------|-------|-----|-------------|------------|
| N9690FCL | Large | 10.228 | 5.629 | N/A | 28.194 lb. | 4.699 |
| N9690FCM | Medium | 9.843 | 5.355 | N/A | 18.996 lb. | 3.166 |
| N9690FCXL | X - Large | 11.024 | 5.827 | N/A | 30.114 lb. | 5.019 |
| N9690FCXXL | XX - Large | 11.417 | 6.141 | N/A | 31.608 lb. | 5.268 |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved