

V-SERIES™ Fall Protection

V-FORM+ Harness
& V-EDGE™ Personal Fall Limiters



As you and your customers return to work in the 'new normal' with additional guidelines and requirements, it's still just as important as always to have the proper equipment to help support safety when working at heights.

To support you in your conversations with customers around Fall Protection needs, samples of the V-FORM+ Harness and V-EDGE Personal Fall Limiter are being provided.

Target Markets for both of these products include:

- Construction — Heavy and Commercial
- General Industry
- OGP

The following bulletin provides differentiating benefits of these products along with associated part numbers that are stocked by MSA.

If you have additional questions, please reach out to your local MSA sales manager, or contact our Customer Service department at us.cs@msasafety.com.

WE KNOW WHAT'S AT STAKE.

V-EDGE 8 ft. (2.4 m) Personal Fall Limiters



Simplified Selection



The V-EDGE PFL can be used in a variety of applications where sharp edge hazards are a concern, making product selection simple.

Easy to Connect



Get to work faster. Save time and frustration with a sleek and simple locking pin attachment.

Lower Cost of Ownership



With a stainless steel housing and protective cover for the energy absorber, the V-EDGE PFL is built to fight the toughest elements, saving you time and money on product replacements.

Markets

- Construction
- General Industry
- Oil and Gas

Applications

- Leading Edge Work

V-FORM+ Standard Harness

Part Number	D-Ring Configuration			Size				Leg Buckle Type		Padding		Standards ANSI Z359.11/ CSA Z259.10/ OSHA
	Back	Back, Hips	Back, Chest	XSM	STD	XLG	SXL	Tongue Buckle	Shoulder			
10206085	■			■				■	■		■	
10205845	■				■			■	■		■	
10206086	■					■		■	■		■	
10206087	■						■	■	■		■	
10206088		■		■				■	■		■	
10206089		■			■			■	■		■	
10206090		■				■		■	■		■	
10206091		■					■	■	■		■	
10206092			■	■				■	■		■	
10206093			■		■			■	■		■	
10206094			■			■		■	■		■	
10206095			■				■	■	■		■	



P/N 10206093



P/N 10206161

V-FORM+ Construction Harness

Part Number	D-Ring Configuration			Size				Leg Buckle Type		Padding		Standards ANSI Z359.11/ CSA Z259.10/ OSHA
	Back	Back, Hips	Back, Chest	XSM	STD	XLG	SXL	Tongue Buckle	Shoulder			
10206160		■		■				■			■	
10206161		■			■			■			■	
10206162		■				■		■			■	
10206163		■					■	■			■	



P/N 63062-00A (left)
P/N 63162-00A (right)

V-EDGE Personal Fall Limiter

Part Number	Type		Line Length	Line Type	Anchorage Connection	Harness Connection	Standards		
	Single-Leg	Twin-Leg					ANSI	OSHA	CSA
63062-00A	■		8 ft. (2.4 m)	Cable	AL36CL Snaphook	Locking Pin	■	■	
63062-00E	■		8 ft. (2.4 m)	Cable	36CS Snaphook	Locking Pin	■	■	
63062-00ACA	■		8 ft. (2.4 m)	Cable	AL36CL Snaphook	Locking Pin			■
63062-00ECA	■		8 ft. (2.4 m)	Cable	Swivel Snaphook	Locking Pin			■
63162-00A		■	8 ft. (2.4 m)	Cable	AL36CL Snaphook (2)	Locking Pin	■	■	
63162-00E		■	8 ft. (2.4 m)	Cable	36CS Snaphook (2)	Locking Pin	■	■	
63162-00F		■	8 ft. (2.4 m)	Cable	36CL Snaphook (2)	Locking Pin	■	■	
63162-00ACA		■	8 ft. (2.4 m)	Cable	AL36CL Snaphook (2)	Locking Pin			■
63162-00ECA		■	8 ft. (2.4 m)	Cable	Swivel Snaphook (2)	Locking Pin			■
63162-00FCA		■	8 ft. (2.4 m)	Cable	36CL Snaphook (2)	Locking Pin			■

Note: This Bulletin contains only a general description of the products shown. While product uses and performance capabilities are generally described, the products shall not, under any circumstances, be used by untrained or unqualified individuals. The products shall not be used until the product instructions/user manual, which contains detailed information concerning the proper use and care of the products, including any warnings or cautions, have been thoroughly read and understood. Specifications are subject to change without prior notice.

MSA operates in over 40 countries worldwide. To find an MSA office near you, please visit MSAsafety.com/offices.