

SHOWA  
**4561**

Engineered to endure, SHOWA 4561 combines DuPont™ Kevlar® cut-resistance with Zorb-IT® oil grip to deliver cut, abrasion and flame resistance, without sacrificing comfort or grip. Utilizing SHOWA's renowned ergonomic design, 4561 naturally contours to your hand for maximum precision and dexterity.

**[ FEATURES**

- 15-gauge engineered liner made with Kevlar®
- ANSI Cut Resistance Level A4
- Sponge nitrile palm finish
- Ergonomic design
- Lightweight, seamless knit

**[ BENEFITS**

- High cut and abrasion resistance
- Kevlar® liner is inherently flame resistant
- Lightweight, breathable liner allows warm air and moisture from inside to escape, keeping your hands dry and comfortable
- Zorb-IT foam nitrile palm finish absorbs oil to increase grip and durability in oily environments
- Ergonomically designed to replicate the hand's natural curves for easy movement and comfortable, continuous wear
- Seamless knit liner increases dexterity

**[ INDUSTRY**



**Automotive**



**Engineering**



**Glass**



**Manufacturing**



**Mechanical**



**Metallurgy**

**[ IDEAL APPLICATIONS**

- Automotive repairs and maintenance
- Light assembly of oil-coated pieces
- Assembly dry and oily parts
- Bottling
- Handling glass and windows
- White goods
- HVAC



**TAA PRODUCTS**

**MADE IN USA**

**MATERIAL**

- Kevlar
- Seamless knit

**COATING**

- Foam nitrile

**GRIP**

- Sponge

**STANDARDS**



SHOWA  
**4561**



**PACKAGING**

- 12 Pair per polybag
- 6 Polybags per case
- 12 Pair per case



**SIZES**

- 6/S
- 7/M
- 8/L
- 9/XL
- 10/XXL



**COLOUR**

- Yellow/black



[ YOU MIGHT ALSO BE INTERESTED IN

SHOWA  
**S-TEX 581**



**MATERIAL**  
Kevlar

**COATING**  
Foam nitrile

SHOWA  
**257**



**MATERIAL**  
Aramid knit

**COATING**  
Foam nitrile

SHOWA  
**234**



**MATERIAL**  
HPPE

**COATING**  
Nitrile

SHOWA  
**S-TEX 303**



**MATERIAL**  
Kevlar

**COATING**  
Latex

[ **USER INSTRUCTIONS**

Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light.

[ **DISCLAIMER**

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

**Get in touch**

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAGroup.com

© SHOWA Group 2018 | All rights reserved