

K2000 SERIES

INDUSTRIAL FEATURES


The K2000 is 20" in depth and ready to handle all your day to day needs. Durability comes standard so you get demanding jobs done time and time again.



Model 297XB:
7-Drawer
Industrial Cabinet

Model 297XR:
7-Drawer
Industrial Cabinet

Double wall construction



Smooth operating ball-bearing drawer slides range from 120-240 lbs.



High security tubular locking system




Heavy-duty 5" x 2" roller bearing casters with 350 lb. capacity per caster



Tubular steel end handle



AVAILABLE COLORS



INDUSTRY SOLUTIONS

The K2000 Series is best used in the following:



INDUSTRIAL 34" & 29" CABINETS/SIDE CABINET

K2000 SERIES



2805X
5-DRAWER TOP CHEST

- Fits 29" or 34" wide roller cabinets
- Ball bearing drawer slides



205X
5-DRAWER SIDE CABINET

- Fits 295X, 297X, 348X
- Ball bearing slides
- Hangs on either side of rolling cabinet



348X
8-DRAWER CABINET

- 5" x 2" roller bearing casters hold up to 350 lbs. each
- Ball bearing drawer slides



297X
7-DRAWER CABINET

- 5" x 2" Roller bearing casters hold up to 350 lbs. each
- Ball bearing drawer slides



295X
5-DRAWER CABINET

- Swing-Down panel conceals & secures spacious storage compartments
- 5" x 2" Roller bearing casters hold up to 350 lbs. each
- Ball bearing drawer slides

PART #	SPECIFICATIONS	STEEL GAUGE									
		DRS.	WIDTH	DEPTH	HEIGHT	LINER *	NET / SHIP WT.	STORAGE	CAPACITY	BODY	DRAWERS
295X	5-Drawer Cabinet	5	29"	20"	35"	-	133 / 145 lbs.	9,720 cu. in.	-	18 ga	20 ga
	Drawers	3	25"	18 1/2"	1 5/8"	84030	-	-	120 lbs.	-	20 ga
		2	25"	18 1/2"	3 5/8"	84030	-	-	120 lbs.	-	20 ga
	Compartment	-	26 1/8"	18 3/8"	11 1/4"	-	-	-	120 lbs.	-	20 ga
297X	7-Drawer Cabinet	7	29"	20"	35"	-	153 / 165 lbs.	10,235 cu. in.	-	18 ga	20 ga
	Drawers	3	25"	18 1/2"	1 5/8"	84030	-	-	120 lbs.	-	20 ga
		3	25"	18 1/2"	3 5/8"	84030	-	-	120 lbs.	-	20 ga
		1	25"	18 1/2"	5 5/8"	84030	-	-	120 lbs.	-	20 ga
348X	8-Drawer Cabinet	8	34"	20"	39"	-	206 / 228 lbs.	14,319 cu. in.	-	18 ga	20 ga
	Drawers	3	30"	18 1/2"	1 5/8"	84027	-	-	120 lbs.	-	20 ga
		4	30"	18 1/2"	3 5/8"	84027	-	-	120 lbs.	-	20 ga
		1	30"	18 1/2"	5 5/8"	84027	-	-	120 lbs.	-	20 ga
2805X	5-Drawer Top Chest	5	29"	20"	16 1/2"	-	87 / 96 lbs.	4,872 cu. in.	-	18 ga	20 ga
	Drawers	4	25"	18 1/2"	1 5/8"	84030	-	-	120 lbs.	-	20 ga
		1	25"	18 1/2"	3 5/8"	84030	-	-	120 lbs.	-	20 ga
205X	5-Drawer Side Cabinet	5	13 5/8"	20"	29 1/6"	-	102 / 102 lbs.	4,073 cu. in.	-	18 ga	20 ga
	Drawers	1	9 3/4"	18 1/2"	1 5/8"	84032	-	-	120 lbs.	-	20 ga
		3	9 3/4"	18 1/2"	3 5/8"	84032	-	-	120 lbs.	-	20 ga
		1	9 3/4"	18 1/2"	9 5/8"	84032	-	-	240 lbs.	-	20 ga

* Liners sold separately



AVAILABLE COLORS

Customize the color of your products. Simply place one of the abbreviations at the end of the model number.



MADE IN THE USA