



Cut



Medium Duty

Professional heavy laborers told us what they needed... and we delivered.

- Intercept Technology[®] for 6 times more cut protection than standard leather gloves*
- Stainless steel and Kevlar[®] fibres provide EN388 level 3 cut protection
- Gel padding reduces vibrations and impacts. Foam nitrile for advanced grip in wet or dry conditions
- Ergonomic and breathable: gloves stay on longer for more tasks

*Results based on Ansell's internal results of the ActivArmr liner with Intercept Technology[®] vs. standard leather gloves (3/11).



Industries

- Mining
- Oil and gas

Applications

- Positioning
- Operating of heavy machinery
- Scaffolding
- Hydraulic set and testing
- Crushing and unloading ore
- Primary grinding
- Hydraulic repair
- Product inspection
- Conveyer and longwall maintenance
- General pumping work
- Handling of tools
- Valve - line maintenance and repair
- Handling jagged metal
- Equipment maintenance Scaffolding Pipe handling and insulation Plumbing and sand blasting
- Heavy machine operation

Technologies



Performance Standards & Regulatory Compliance



EN 388:2003



REACH Compliant

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENG TH	PACKAGE
ActivArm® 97-003	Palm Coated, Foam Nitrile, Nylon, Spandex, Stainless steel, Kevlar®, Velcro®	13	9, 10, 11	269-278 mm	• 12 pairs in a bag; 6 bags in a carton



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro, Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.