



SCIENCE* KIMWIPES* Delicate Task Wipers

Product Information

Code	Color	Ply	Put-Up	Sheet Size	Sheets/Pack	Packs/Case	Sheets/Case
34120	White	1	POP-UP* Box	4.4" x 8.4"	280	30	8400
34155	White	1	POP-UP* Box	4.4" x 8.4"	280	60	16800
34133	White	1	POP-UP* Box	11.8" x 11.8"	196	15	2940
34256	White	1	POP-UP* Box	14.7" x 16.6"	140	15	2100
34705	White	2	POP-UP* Box	11.8" x 11.8"	119	15	1785
34721	White	2	POP-UP* Box	14.7" x 16.6"	90	15	1350
34743	White	3	POP-UP* Box	11.8" x 11.8"	119	15	1785



Physical Properties

The following are current, subject to change at any time without notice. Physical property data is as produced; subsequent storage conditions and the age of the product, which are beyond Kimberly-Clark's control, may affect the properties of the product as received. Test results of competitive product are single sample of the product provided by the customer.

Property	Target Value 1-Ply	Target Value 2-Ply	Target Value 3-Ply	Testing Method
Water Capacity (g/4"x4")	1.1	1.8	2.8	STM 2401
Oil Capacity (g/4"x4")	0.6	1.4	1.9	STM 2401
Tensile Strength MD Dry (g/3in.)	1500	3000	4425	STM 5500
Tensile Strength CD Wet (g/3 in.)	425	580	950	STM 5500
Tensile Strength CD Dry (g/3 in.)	1500	2300	3495	STM 5500
MD Stretch (%)	{30}	NA	NA	STM 5500

Workmanship Requirements

Wipers shall be made in accordance with reasonable industry practice with respect to holes, tears, wrinkles, cleanliness, odors and foreign materials or dirt. Edges shall be cleanly cut. For additional information: 1-888-346-4652 or kimtech@kcc.com

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms of verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

©/™Trademarks of Kimberly-Clark Worldwide, Inc. or its affiliates. Marques déposées de Kimberly-Clark Worldwide, Inc. ou de ses filiales. © 2013 KCWW.